




Search bar: What can we help you find?

- Products
- Industries
- Resources
- About TE
- My Account
- Innovation
- Support Center

Home > Products > RF & Coax > Product Feature Selector > Product Details

# 1061001-1 Product Details

Share | Print | Email



1061001-1

TE Internal Number: 1061001-1  
Active

## MCX (OSX) RF Connectors

Always EU RoHS/ELV Compliant (Statement of Compliance)

### Product Highlights:

- Connector - RF
- Jack
- Body Style = Straight
- Applies To Printed Circuit Board
- Without Panel Mount Retention

[View all Features](#)

- [Add to My Part List](#)
- [Request Sample](#)
- [Find Similar Products](#)
- [Buy Product](#)

### Quick Links

- ▶ [Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

## Documentation & Additional Information

### Product Drawings:

- [OSX PRINTED WIRING BOARD JACK RECEPTACLE STRAIGHT ... \(PDF, English\)](#)

### Catalog Pages/Data Sheets:

- None Available

### Product Specifications:

- None Available

### Application Specifications:

- None Available

### Instruction Sheets:

- None Available

### CAD Files:

- None Available

### Related Products:

- [Tooling](#)

[List all Documents](#)

## Product Features (Please use the Product Drawing for all design activity)

### Product Type Features:

- [Product Type](#) = Connector - RF
- [Gender](#) = Jack
- [PCB Mount Retention](#) = With
- [Connector Family](#) = OSX
- [Dielectric Material](#) = TFE Fluorocarbon

### Mechanical Attachment:

- [Panel Mount Retention](#) = Without

### Electrical Characteristics:

- [Connector Impedance \(Ω\)](#) = 50

### Body Features:

- [Body Style](#) = Straight
- [Body Plating](#) = Gold
- [Body Material](#) = Brass

### Contact Features:

- [Center Contact Plating](#) = Gold
- [Center Contact Material](#) = Beryllium Copper
- [Captured Center Contact](#) = With

### Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C, Reflow solder capable to 245°C, Reflow solder capable to 260°C, Pin-in-Paste capable to 245°C, Pin-in-Paste capable to 260°C
- [RoHS/ELV Compliance History](#) = Always was RoHS compliant

### Conditions for Usage:

- [Applies To](#) = Printed Circuit Board

### Other:

- [Brand](#) = AMP

## Corporate Information

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)
- [Terms & Conditions](#)
- [Privacy Policy](#)

## Quick Links

- [Distributor Inventory](#)
- [Product Cross Reference](#)
- [Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

## Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Knowledge Base](#)
- [Manage Your Account](#)

## Keep Me Informed

