



**CONNECTORS**

**RIBBON CABLE CONNECTORS**



✓ Active

TE CONNECTIVITY (TE)

## 034 UNIV HDR SP 4V 30DP STD

AMP-LATCH | Universal Headers

111008-8

TE Internal Number: 111008-8

Not EU RoHS Compliant

Not Yet Reviewed for EU ELV

**Connector System** Board-to-Board

**Number of Positions** 34

**Centerline (Pitch)** 2.54 mm [ .1 in ]

**PCB Mount Retention** Without

**PCB Mount Retention Type** Screw Mount

[↓ PRODUCT DRAWING](#)  
English

[↓ 3D PDF](#)

### DOCUMENTATION

Product Drawings

**AMP-LATCH UNIVERSAL HEADER, .025 SQ POST, .100 X .100CL, STRAIGHT, FOR VAPOR-PHASE APPLICATIONS**

PDF (TIFF AVAILABLE)

English

CAD Files

**3D PDF**

PDF

3D

**Customer View Model**

2D\_DXF.ZIP

English

## Customer View Model

3D\_IGS.ZIP

English

## Customer View Model

3D\_STP.ZIP

English

---

Product Specifications

Product Specification

## AMP-LATCH And IDC Header Connectors, .100 X .100 Inch Grid

PDF

English

Qualification Test Report

## Connector, AMP-LATCH Header, .100 X .100 Inch Grid

PDF

English

---

Instruction Sheets

Instruction Sheet (U.S.)

## AMP INSTALLATION PROCEDURES FOR AMP-LATCH UNIVERSAL HEADER ASSEMBLIE

PDF

English

## AMP INSTALLATION PROCEDURES FOR AMP-LATCH UNIVERSAL HEADER ASSEMBLIE

TIF

English

---

## FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

---

Product Type Features

**Header Type** Universal Ejection Pin Headers

**Connector System** Board-to-Board

**PCB Mounting Orientation** Vertical

**Shrouded** Yes

**Row-to-Row Spacing** 2.54 mm [.1 in]

**Connector Style** Receptacle

**Profile** Standard

**Connector & Contact Terminates To** Printed Circuit Board

**Connector Type** Header

**Board Standoff** Without

**Product Type** Connector

---

Configuration Features

**Number of Positions** 34

**Number of Rows** 2

**Ejection Latches** Without

---

## Electrical Characteristics

**Operating Voltage (VAC)** 250

**Insulation Resistance (MΩ)** 5000

---

## Body Features

**Post Size** .64 mm [ .025 in ]

**Daisy Chain** Without

---

## Contact Features

**Solder Tail Contact Plating Material** Tin-Lead

**Contact Shape** Square

**Contact Current Rating (Max) (A)** 1

**Contact Mating Area Plating Material** Gold

**Contact Type** Pin

**Contact Termination Area Plating Thickness** 2.54 μm [ 100 μin ]

**Contact Transmits (Typical)** Signal (Data)

**Contact Design** Solder Dip

**Contact Termination Area Plating Material** Gold Flash over Palladium Nickel

**Contact Mating Area Plating Thickness (μin)** 30

---

## Termination Features

**Termination Method to PC Board** Through Hole (SMT Compatible)

**Termination Post Length** 2.79 mm [ .11 in ]

---

## Mechanical Attachment

**Panel Mount Retention** Without

**PCB Mount Alignment** With

**PCB Mount Retention** Without

**PCB Mount Retention Type** Screw Mount

**Mating Alignment Type** Center, Dual Polarizing Bar

**Mating Connector Lock** Without

**Mating Alignment** With

**Mating Retention** Without

**Polarization** With

---

## Housing Features

**Centerline (Pitch)** 2.54 mm [ .1 in ]

**Housing Material** Thermoplastic

**Housing Color** Red

**Housing Style** 4-Sided

---

## Dimensions

**Shrouded End Dimension** 3.81 mm [ .15 in ]

**Height** 13.94 mm [ .55 in ]

**Length** 62.48 mm [ 2.46 in ]

---

## Usage Conditions

**Operating Temperature Range (°C)** -65 – 105

**Temperature Rating** High

---

Industry Standards

**UL Flammability Rating** UL 94V-0

---

Packaging Features

**Packaging Method** Package

**Packaging Quantity** 50

---

## **PRODUCT COMPLIANCE**



Statement of Compliance

**Statement of Compliance**

PDF

---