

 [Live Product Chat](#)



✓ Active

 [View 3D PDF](#)

Not EU RoHS or ELV Compliant (Find RoHS Compliant Alternates)

- Connector Type = .079 [2.0mm] AMP-LATCH
- Number of Positions = 44
- Receptacle
- Mating Polarization Method = Center
- With Mating Polarization

[View all Features](#) | [Find Similar Products](#)

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)
- ▶ [Request Samples](#)

NEW!

- [RECEPTACLE ASSY, POLARIZED, 2mm CL, AMP-LATCH](#) (PDF, English)

- None Available

- [CONNECTOR, AMP-LATCH, 2 MM, RIBBONCABLE RECEPTACLE \(PDF, English\)](#)

- [AMP-LATCH 2 mm Receptacle Connectors](#) (PDF, English)

- [Connector-Specific Kit f/AMP-LATCH 2mm Receptacle Co...](#) (PDF, English)

- 2D Drawing (DXF, Version L1)
- 3D Model (IGES, Version L1)
- 3D Model (STEP, Version L1)

List all Documents

- Product Line Information

- Tooling

- Connector Type = .079 [2.0mm] AMP-LATCH
- Number of Positions = 44
- Gender = Receptacle
- Mating Polarization Method = Center
- Mating Polarization = With
- Mounting Ears = Without
- PCB Retention Feature = No
- Mating Connector Lock = Without
- Strain Relief = Without
- With Cover Preassembled = Yes
- Cover Type = Feed Thru
- Comment = Accepts 28 AWG [0.08-0.09mm²] ribbon cable, 0.61-0.97 [.024-.038] thick PVC 1.00 [.039] pitch.

- Solder Tail Contact Plating = Tin-Lead

- Centerline, Matrix (mm [in]) = 2.00 x 2.00
[.079 x .079]

- Contact Mating Area Plating Material = Gold (30)
- Contact Material = Beryllium Copper

- Housing Color = Black
- Housing Material = Polyester
- Housing Flammability Rating = UL 94V-0

- Cable Stop = Without

- RoHS/ELV Compliance = Not ELV/RoHS compliant
- Lead Free Solder Processes = Not relevant for lead free process

- Terminate To = Ribbon Cable

- Brand = AMP