

 Live Product Chat US Only
8:30am - 5pm ET, Mon - Fri



 Active

Always EU RoHS/ELV Compliant (Statement of Compliance)

- ? Connector
- ? Connector Type = Header (Cap)
- ? Number of Positions = 16
- ? Phosphor Bronze Contact Material
- ? Selective Tin Contact Mating Area
- Plating Material

[View all Features](#) | [Find Similar Products](#)

[Check Pricing & Availability](#)
[Search for Tooling](#)
[Product Feature Selector](#)
[Contact Us About This Product](#)

? 16P CAP HOUSING ASSY (V -TYPE) DUAL LINE INTERLOCK CO...
(TIF, Japanese)

? None Available

Dual Line Interlock Connector (TIF, English)

? None Available

? None Available

? None Available

List all Documents

? Product Line Information

? Tooling

- ? Product Type = Connector
- ? Connector Type = Header (Cap)
- ? Number of Positions = 16
- ? PCB Mount Angle = Vertical
- ? Post Size (mm [in]) = 0.64 [.025]

? Lock Plate/Double Lock Plate = Double Lock Plate

? Number of Rows = 2

? Row Spacing (mm [in]) = 4.60 [0.818]

- ? Contact Material = Phosphor Bronze
- ? Contact Mating Area Plating Material = Selective Tin
- ? Contact Centerline Spacing (mm [in]) = 3.00 [0.118]
- ? Contact Shape = Square

? Housing Material = Nylon
 ? Housing Color = Black
 ? Housing Flammability Rating = UL 94V -2

- ? RoHS/ELV Compliance = RoHS compliant, ELV compliant
- ? Lead Free Solder Processes = Wave solder capable to 240°C
- ? RoHS/ELV Compliance History = Always was RoHS compliant

? Terminate To = Printed Circuit Board

? Packaging Method = Loose Piece

? Brand = Tyco Electronics