


[My Cart](#) | [My Part Lists](#) | [Sign In/Register](#)[English \(Change\)](#)Search by Keyword or Part #  

## 1544504-1 Product Details

### Have a Question?

Chat with a Product Information Specialist

**1544504-1**

TE Internal Number: 1544504-1

[Active](#)[View 3D PDF](#)

### FASTON Uninsulated Receptacles & Housings

[Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

#### Product Highlights:

- Product Classification = Connectors - Terminals and Splices
- Terminal
- Terminal Type = Receptacle
- Mating Area Interface Dimensions = 6.35 x 0.80 mm
- Board Mount = No

[View all Features](#)

### Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

[Add to My Part List](#)[Request Sample](#)[Find Similar Products](#)[Buy Product](#)

### Documentation & Additional Information

#### Product Drawings:

- [CLIP DE SECURITE 6.35 capacite 1.5 a 3 mm2](#) (PDF, English)

#### Catalog Pages/Data Sheets:

- None Available

#### Product Specifications:

- None Available

#### Application Specifications:

- None Available

#### Instruction Sheets:

- None Available

#### CAD Files: [\(CAD Format & Compression Information\)](#)

- [2D Drawing](#) (DXF, Version B)
- [3D Model](#) (IGES, Version B)
- [3D Model](#) (STEP, Version B)

[List all Documents](#)

#### Additional Information:

- [Product Line Information](#)

#### Related Products:

- [Tooling](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- Product Classification = Connectors - Terminals and Splices
- Product Type = Terminal
- Terminal Type = Receptacle
- Mating Area Interface Dimensions (mm [in]) = 6.35 x 0.80 [ .250 x .031 ]
- Receptacle Style = Straight
- Insulation Support = Insulation Support
- Wire/Cable Type = Stranded
- Insulation Diameter (mm [in]) = 4.40 [ .173 ]
- Insertion Force = Low
- Material = Brass
- Finish = None
- Crimp Type = F-Crimp

#### Mechanical Attachment:

- Board Mount = No

#### Body Related Features:

- Weld Tab = Without
- Wire Range (mm [AWG]) = 1.00-2.50<sup>2</sup> [17-13]

#### Industry Standards:

- RoHS/ELV Compliance = RoHS compliant, ELV compliant
- Lead Free Solder Processes = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

#### Packaging Related Features:

- Packaging Method = Strip
- Packaging Quantity = 6,000

#### Other:

- For Hermetic Header Tab = No
- Line = Microlock
- Brand = Tyco Electronics



### Corporate Information

[Who We Are](#)[Investors](#)[News Room](#)[Supplier Portal](#)[Careers](#)

### Quick Links

[Check Distributor Inventory](#)[Cross Reference](#)[Find Documents & Drawings](#)[Product Compliance Support Center](#)[Site Map](#)

### Customer Support

[Email or Chat with Us](#)[Find a Phone Number](#)[Search Knowledge Base](#)[Manage Your Account](#)

### Sign up for our eNewsletter

Enter your email address

### Follow Us On:

Twitter Facet Flickr Linke YouTi

Visit Us On:



