


1734172-1 Product Details



1734172-1

TE Internal Number: 1734172-1
Active

 [View 3D PDF](#)

Audio/Phone Jack Connectors

 [Always EU RoHS/ELV Compliant](#) ([Statement of Compliance](#))

Product Highlights:

- Telephone Application
- Not Stacked
- Number of Positions = 3
- PCB Mount Angle = Right Angle
- Tin Contact Plating

[View all Features](#)

 [Live Product Chat](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- [DC POWER JACK, 3P](#) (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files: ([CAD Format & Compression Information](#))

- [2D Drawing](#) (DXF, Version 0)
- [3D Model](#) (IGES, Version 0)
- [3D Model](#) (STEP, Version 0)

[List all Documents](#)

Related Products:

- [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Stacked = No
- Number of Positions = 3
- PCB Mount Angle = Right Angle

Termination Related Features:

- Solder Tail Contact Plating = Tin
- Tail Length (mm [in]) = 4.1 [0.161]

Body Related Features:

- Mating Hole Diameter (mm [in]) = 2.00 [0.080]

Contact Related Features:

- Contact Plating = Tin
- Contact Material = Copper Alloy

Housing Related Features:

- Housing Color = Black
- Housing Material = Thermoplastic
- Housing Flammability Rating = UL 94V-0

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- RoHS/ELV Compliance History = Always was RoHS compliant

Operation/Application:

- Application = Telephone

Packaging Related Features:

- Packaging Method = Bag

Other:

- Brand = Tyco Electronics