




1734577-2 Product Details

[Share](#) | [Print](#) | [Email](#)


1734577-2

TE Internal Number: 1734577-2
✔ Active

[View 3D PDF](#)

PCB Mounted Jacks - Single Port, Multi-port and Stacked

✔ Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Connector
- Preloaded
- Single Port Configuration
- 1 x 1 Jack Configuration
- Jack Type = RJ45

[View all Features](#)

Quick Links

- ▶ [Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#) | [Request Sample](#) | [Find Similar Products](#) | [Buy Product](#)

Documentation & Additional Information

Product Drawings:

- MODULAR JACK, RJ45, 8P8C, DIP TYPE. (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files: (CAD Format & Compression Information)

- 2D Drawing (DXF, Version C)
- 3D Model (IGES, Version C)
- 3D Model (STEP, Version C)

Additional Information:

- Product Line Information

Related Products:

- Tooling

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Product Type = Connector
- Jack Type = RJ45
- PCB Mounting Orientation = Top Entry (Vertical)
- PCB Mount Style = Through Hole
- Termination Method to PC Board = Solder
- Performance Category = Cat 3
- LED = With
- Grounding Options = PCB Ground
- Panel Stops = Without
- Keyed = No
- Profile = Standard
- Color = Black
- Shield Material = Brass

Mechanical Attachment:

- Panel Mount Retention = Without
- Flanged = No

Electrical Characteristics:

- Shielded = Yes

Termination Features:

- Solder Tail Contact Plating = Gold Flash over Nickel

Dimensions:

- Height (mm [in]) = 16.50 [0.650]
- PCB Tail Length (mm [in]) = 3.25 [0.1281]
- PCB Thickness, Recommended (mm [in]) = 1.57 [0.062]

Body Features:

- Inverted Jack Face = No
- Shield Plating = Nickel
- LED Lightpipe Material = Epoxy Resin
- PCB Ground Tab Location (mm [in]) = 3.85 [0.152]

Contact Features:

- Contact Plating, Mating Area, Material = Gold (15)
- Contact Base Material = Phosphor Bronze

Housing Features:

- Housing Material = High Temperature Thermoplastic
- UL Flammability Rating = UL 94V-0

Configuration Features:

- Preloaded = Yes
- Port Configuration = Single
- Jack Configuration = 1 x 1
- Number of Positions = 8
- Number of Contacts Loaded = 8
- Number of PCB Ground Tabs = 2

Industry Standards:

- RoHS/ELV Compliance = RoHS compliant, ELV compliant
- Lead Free Solder Processes = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- RoHS/ELV Compliance History = Always was RoHS compliant

Identification Marking:

- LED Position 1 Color = Green
- LED Position 2 Color = Yellow
- LED Position 3 Color = None

Packaging Features:

- Packaging Method = Tray
- Packaging Quantity = 100/Tray

Product Availability:

- Region = Asia, North America

Other:

- Brand = TE Connectivity

Corporate Information

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)
- [Terms & Conditions](#)
- [Privacy Policy](#)

Quick Links

- [Distributor Inventory](#)
- [Product Cross Reference](#)
- [Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Knowledge Base](#)
- [Manage Your Account](#)

Keep Me Informed

