




1757838-2 Product Details

[Share](#) | [Print](#) | [Email](#)


1757838-2

TE Internal Number: 1757838-2

Active

[View 3D PDF](#)

Subminiature D Pins/Sockets for MIL-C-24308 and MIL-C-39029

Always EU RoHS/ELV Compliant ([Statement of Compliance](#))

Product Highlights:

- Connector
- Product Series = 109
- Connector Style = Receptacle
- Contact Type = Socket
- Density = Standard

[View all Features](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#) | [Request Sample](#) | [Find Similar Products](#) | [Buy Product](#)

Documentation & Additional Information

Product Drawings:

- [RECEPTACLE ASSEMBLY,AMPLIMITE,RT ANGLE, SERIES 109,S...](#) (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files: ([CAD Format & Compression Information](#))

- [2D Drawing](#) (DXF, Version C)
- [3D Model](#) (IGES, Version C)
- [3D Model](#) (STEP, Version C)

[List all Documents](#)

Additional Information:

- [Product Line Information](#)

Additional Product Images:

- [Insert Arrangement](#)

Related Products:

- [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Product Type](#) = Connector
- [Product Series](#) = 109
- [PCB Mounting Orientation](#) = Right Angle
- [Shell Size](#) = 2
- [Shell Material](#) = Steel
- [Mounting Hole Diameter \(mm \[in\]\)](#) = 2.92-3.18 [.115-.125]

Termination Features:

- [Termination Post Length \(mm \[in\]\)](#) = 3.95 [0.156]

Body Features:

- [Number of Positions](#) = 15
- [Insert Arrangement](#) = MS18273-1
- [Blindmate](#) = No
- [Non-Magnetic](#) = No
- [Rear Grommet](#) = No
- [Power/Signal/Coax Combination](#) = No
- [Shell Plating](#) = Zinc
- [Post Diameter \(mm \[in\]\)](#) = 0.76 [0.030]
- [Mount Style](#) = Mounting Holes

Contact Features:

- [Contact Type](#) = Socket
- [Contact Size](#) = 20
- [Contact Base Material](#) = Brass or Beryllium Copper
- [Contact Plating, Mating Area, Material](#) = Gold

Housing Features:

- [Connector Style](#) = Receptacle

Configuration Features:

- [Density](#) = Standard

Industry Standards:

- [Government/Industry Qualification](#) = Yes
- [Government/Industry Part Number](#) = M24308/23-32
- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- [RoHS/ELV Compliance History](#) = Always was RoHS compliant
- [NASA Qualification](#) = No

Conditions for Usage:

- [Applies To](#) = Printed Circuit Board

Other:

- [Brand](#) = Tyco Electronics

Corporate Information

- [Who We Are](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)

Quick Links

- [Check Distributor Inventory](#)
- [Cross Reference](#)
- [Find Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Search Knowledge Base](#)
- [Manage your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

