

1 - 1825099

- 0

Product Details

1 - 1825099

- 0

TE Part Number: 1 - 1825099 - 0

✔

Active

🔖

Add to Part List

Pushbutton Switches

Always EU RoHS/ELV Compliant

(

Statement of Compliance

)

Product Highlights:

⌵ Switch - Mechanical

⌵ Not Tactile

⌵ Double Pole - Double Throw Configuration (Pole - Throw)

⌵ Contact Rating = 0.4VA

⌵ Operating Function = Momentary

View all Features

|

Find Similar Products

Live Product Chat

Quick Links

Check Pricing & Availability

Search for Tooling

Product Feature Selector

Contact Us About This Product

Documentation & Additional Information	
Product Drawings: ⌵ None Available Catalog Pages/Data Sheets: ⌵ None Available Product Specifications: ⌵ None Available Application Specifications: ⌵ None Available Instruction Sheets: ⌵ None Available CAD Files: ⌵ None Available	Additional Information: ⌵ Product Line Information Related Products: ⌵ Tooling

Product Features (Please use the Product Drawing for all design activity)	
Product Type Features: ⌵ Product Type = Switch - Mechanical ⌵ Tactile = No ⌵ Configuration (Pole - Throw) = Double Pole - Double Throw ⌵ Mount Angle = Vertical ⌵ Termination Type = Printed Circuit ⌵ Actuator Style = Round Electrical Characteristics: ⌵ Contact Rating = 0.4VA Body Related Features: ⌵ Series = TPD ⌵ Mount Style = Through -Hole ⌵ Actuator Length (mm [in]) = 4.01 [0.158] ⌵ Actuator Profile = Extended ⌵ Actuator Color = Black ⌵ Bushing Diameter = 6.35 [.250] ⌵ Case Material = Polyester ⌵ Actuator Material = Polyamide Contact Related Features: ⌵ Contact Plating = Gold over Nickel Housing Related Features: ⌵ Process Sealed = No ⌵ Low Profile = No ⌵ Bushing Style = Unthreaded	Configuration Related Features: ⌵ Operating Function = Momentary ⌵ Ganged = No ⌵ ESD Grounding Terminal = Without ⌵ Actuator Force (g [oz]) = 50.00 - 400.00 [1.770 - 14.120] ⌵ Number of Actuators = Single ⌵ Illuminated = No ⌵ Dust Proof = No ⌵ Support Bracket = Without ⌵ Snap Action = Without Industry Standards: ⌵ RoHS/ELV Compliance = RoHS compliant, ELV compliant ⌵ Lead Free Solder Processes = Wave solder capable to 240°C, Wave solder capable to 260° C, Wave solder capable to 265°C ⌵ RoHS/ELV Compliance History = Always was RoHS compliant Conditions for Usage: ⌵ Temperature Rating = High Packaging Related Features: ⌵ Packaging Method = Loose Piece Other: ⌵ Brand = Alcoswitch

Provide Website Feedback

|

Need Help?

Home

|

Customer Support

|

Suppliers

|

Site Map

|

Privacy Policy

|

Browser Support

© 2008 Tyco Electronics Corporation All Rights Reserved