

# 11000 series

## Professional toggle switches - threaded bushing Ø 6,35 (1/4)

### Specifications

#### ELECTRICAL SPECIFICATIONS

- Max. current/voltage rating with resistive load : Peak currents, refer to "Special options".
  - silver contacts (A-AD2-X780) : 2A 250VAC - 4A 125VAC - 4A 30VDC
  - gold contacts (D) : 200mA 250VAC - 400mA 125VAC
- Minimum load : AD2-X780-D contacts : 10mA 50mV, 10µA 5V min.
- Initial contact resistance : 10 mΩ max.
- Insulation resistance : 1.000 MΩ min. at 500VDC
- Dielectric strength :
  - 1.000 Vrms 50 Hz min. between terminals
  - 2.000 Vrms 50 Hz min. between poles and between terminals and frame
- Contact bounce : 2 ms max.
- Electrical life at full load :

Contacts	Max. current/voltage rating	Number of cycles	
		2 positions	3 positions
A	2A 250VAC - 4A 125VAC - 4A 30VDC	50.000	50.000
AD2 X780	2A 250VAC - 4A 125 VAC - 4A 30VDC (Gold plating : 100mA 30VDC max.)	20.000	20.000
D	200mA 250VAC - 400mA 125VAC	80.000	50.000
	Low level or mechanical life	150.000	100.000

#### MATERIALS

- Case : diallylphthalate (DAP)
- Actuator : brass, nickel plated
- Bushing : brass, nickel plated
- Housing : brass, nickel plated
- Contacts
  - A** : silver
  - AD2** : gold plated silver (2 microns gold)
  - X780** : solid rivet - gold plated silver/nickel alloy
  - D** : solid gold rivet
  - X910** : silver/nickel alloy (for peak currents, see "Special options")
- Terminal seal : epoxy

Note : AD2 and X780 contacts can be used for high level applications. In this case, the gold layer is considered only as a protection against oxidation during storage.

#### GENERAL SPECIFICATIONS

- Torque : 1,25 Nm (.92 Ft.lb) max. applied between the 2 nuts
- Standard panel thickness : 2,5 mm (.098) max.
- Operating temperature : -40°C to +85°C

#### RELIABILITY - RUN-IN TEST

Upon request, each individual switch can be submitted to a low level run-in test of 50 or 250 cycles to ensure suitability for special applications requiring a very high level of reliability (military, etc.).

#### AGENCY APPROVALS



CECC 96201-005  
CECC 96201-008

**Availability** : consult factory for details of approved models.  
**Marking** : to order switches marked CECC, complete appropriate box of ordering format.

**Dimensions** : first dimensions are in mm while inches are shown as bracketted numbers.




**Packaging unit** : 25 pieces or 50 pieces depending on models.

# 11000 series

## Professional toggle switches - threaded bushing Ø 6,35 (1/4)

Overview



**NOTICE** : please note that not all combinations of above numbers are available. Refer to the following pages for further information.

### ABOUT THIS SERIES

On the following pages, you will find successively :

- model structure of switches
- options in the same order as in above chart



**Sealing boots** are available to protect the switches against dust and water. They are presented in section H.



**Mounting accessories** : standard hardware supplied with all models : 2 hex nuts 8 (.314) across flats, 1 locking ring and 1 lockwasher. Standard and special hardware available are presented in section I.


# 11000 series

Professional toggle switches - threaded bushing  $\varnothing 6,35$  (1/4)


MODEL  
STRUCTURE



A



- Solder lug, straight PC or right angle terminals
- Epoxy sealed terminals standard



MODEL  
STRUCTURE



Shown with standard lever


## Solder lug terminals - single pole



11136  
11139  
11137  
11138

	I	II	III
ON	-	ON	
ON	OFF	ON	
MOM	OFF	MOM	
ON	OFF	MOM	

→ Keyway




## Solder lug terminals - double pole



11146  
11149  
11147  
11148

	I	II	III
ON	-	ON	
ON	OFF	ON	
MOM	OFF	MOM	
ON	OFF	MOM	

→ Keyway




## Solder lug terminals - three pole



11156  
11159  
11157  
11158

	I	II	III
ON	-	ON	
ON	OFF	ON	
MOM	OFF	MOM	
ON	OFF	MOM	

→ Keyway





# 11000 series

Professional toggle switches - threaded bushing  $\varnothing 6,35$  (1/4)


## Solder lug terminals - four pole



11166  
11169  
11167  
11168

ON	-	ON
ON	OFF	ON
MOM	OFF	MOM
ON	OFF	MOM

→ Keyway




## Straight PC terminals - single pole ▲



11236

ON	-	ON

→ Keyway




## Straight PC terminals - double pole ▲



11246

ON	-	ON

→ Keyway




## Straight PC terminals - three pole ▲



11256

ON	-	ON

→ Keyway








# 11000 series

Professional toggle switches - threaded bushing  $\varnothing 6,35$  (1/4)


## CONTACT MATERIALS



- A** Silver
- AD2** Gold plated silver (2 micron gold)
- D** Solid gold rivet

See "Special options" for contacts X780 (solid silver/nickel rivet) and contacts X910 (for peak currents).

## FINISH



- Blank** Bright chrome finish
- G** Matt black finish on bushing, lever and hardware.



Other finish, consult factory.

## SEALING



Epoxy sealed terminals are standard.



- Blank** No sealing except standard
- K** Front panel sealing by O-ring and sealing washer. Protects the switch against panel water and dust. Panel seal withstands 1 bar pressure and remains sealed even when switch is operated.




① O-ring ② Sealing washer

Sealing by two O-rings, see X408 under "Special options".  
Sealing boots : see section H.

## LEVERS



**Blank**  
Standard




**-26**  
Cylindrical

# 11000 series

Professional toggle switches - threaded bushing  $\varnothing$  6,35 (1/4)




## SPECIAL OPTIONS



**X408** Front panel sealing by two O-rings. Flatted bushing for precise orientation.  
Protects the switch against water and dust.  
Panel seal withstands 1 bar pressure and remains sealed even when switch is operated.



Not available on 11000W model.



**X408**

→ Flat

① O-rings

**X780** Solid rivet, gold plated silver/nickel alloy

**X910** Switches for peak currents

Peak current up to 80A (1 ms) 60VDC - single/double pole




Single pole  
**11136 X910** ON - ON

Double pole  
**11146 X910** ON - ON

- Contacts : solid rivet - silver/nickel alloy (AgNi)
- Max. current/voltage rating :  
3/80A (1 ms) 60VDC - 10.000 cycles  
2/30A 250VAC - 10.000 cycles
- Further specifications and dimensions : see previous pages
- General information on peak currents : see end of catalogue.

## AGENCY APPROVALS



**CECC** CECC 96201-005 (high level - contacts X780)  
CECC 96201-008 (low level - contacts AD2 or D)

**Availability** : consult factory for details of approved models.

**Marking** : to order switches marked CECC , complete above box with "CECC".  
Blank : no agency approval required.