


2007828-2 Product Details

[Share](#) | [Print](#) | [Email](#)


Impact High Density Backplane Connectors

IMP,H,4PR16C,RGOpenNo key,4.9,

2007828-2

TE Internal Number: 2007828-2

Active

Product Highlights [View All](#)

- Connector Style = Header
- 128/Signal, 64/Ground
- 192 Positions
- Header Type = Partially Shrouded
- Board-to-Board Configuration = Right Angle, Vertical

[Pricing & Availability](#)
[Request Sample](#)
[Add to My Part List](#)
[Buy Product through Distributor](#)

Feedback

[Documents](#) | [Features](#) | [Compliance](#)

Please Note:
Use the Product Drawing for all design activity

Product Type Features	
PCB Mount Retention Type	Action/Compliant Tail and Screw(s)
PCB Mount Alignment Type	Locating Post(s)

Electrical Characteristics	
Impedance (Ω)	100
Operating Voltage Reference	AC/DC
Operating Voltage (VAC)	120
Operating Voltage (VDC)	120

Dimensions	
Tail Length (mm [in])	1.2 [0.047]
Length (X-Axis) (mm [in])	36.90 [1.4528]
Width (Z-Axis) (mm [in])	20.80 [0.819]
Profile Height (Y-Axis) (mm [in])	11.95 [0.470]
PCB Hole Diameter (mm [in])	0.46 [0.018]

Body Features	
Header Type	Partially Shrouded

Contact Features	
Contact Type	Pin
Contact Length (mm [in])	4.90 [0.193]
Contact Plating, Termination Area, Material	Matte Tin
Contact Plating, Termination Area, Thickness (µm [µin])	1.27 [50]
Contact Base Material	Copper-Nickel-Silicon
Underplate Material	Nickel
Underplate Material Thickness (µm [µin])	1.27 [50.000]

Housing Features	
Connector Style	Header
End Wall Location	Open
Housing Color	Black
Housing Material	LCP (Liquid Crystal Polymer)

Configuration Features	
Connector Contact Configuration (No. of Pos./Type)	128/Signal, 64/Ground
Number of Positions	192
Number of Differential Pairs Per Column	4
Number of Columns	16
Number of Rows	12
Shrouded	Yes - Partial
Guide Location	Right
Tail Orientation	In-line

Industry Standards	
RoHS/ELV Compliance	RoHS compliant, ELV compliant
Lead Free Solder Processes	Not relevant for lead free process
RoHS/ELV Compliance History	Always was RoHS compliant
UL Rating	Recognized
UL File Number	E28476
UL Flammability Rating	UL 94V-0
CSA Certified	Yes

Environmental	
Operating Temperature (°C [°F])	-55 - +85 [-67 - +185]

Conditions for Usage	
Board-to-Board Configuration	Right Angle, Vertical

Operation/Application	
Industry Application	Networking (Communications)

Packaging Features	
Packaging Method	Tube/Box

Other	
Brand	TE Connectivity

Related Products

Not quite the product you're looking for?

[Find Similar Products](#)

[View Part in Product Feature Selector](#)

[Check for Tooling](#)

