


2-1888291-1 Product Details

[Live Product Chat](#)



2-1888291-1

TE Part Number: 2-1888291-1

[Active](#)

[Add to Part List](#)

FPC (Flexible Printed Circuit) Connectors

[Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- 2.54 mm Centerline
- Number of Positions = 14
- PCB Mount Angle = Vertical
- PCB Mount Style = Thru Hole
- Standard Profile

[View all Features](#) | [Find Similar Products](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- [HEADER ASSY, VERTICAL, SINGLE ROW, FLEXPAC](#) (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Number of Positions](#) = 14
- [PCB Mount Angle](#) = Vertical
- PCB Mount Style = Thru Hole
- Profile = Standard

Termination Related Features:

- Solder Tail Contact Plating = Tin over Nickel

Body Related Features:

- [Centerline \(mm \[in\]\)](#) = 2.54 [0.100]

Contact Related Features:

- Contact Material = Phosphor Bronze
- Contact Mating Area Plating Material = Tin over Nickel

Housing Related Features:

- Housing Flammability Rating = UL 94V-0
- Housing Material = Nylon
- Housing Color = Blue

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- RoHS/ELV Compliance History = Always was RoHS compliant

Other:

- Brand = AMP