


2 - 487378

- 1

Product Details

 **Live Product Chat** US Only
8:30am - 5pm ET, Mon - Fri



2 - 487378

- 1

 [Active](#)

Flexible Film Connectors

[Always EU RoHS/ELV Compliant](#) ([Statement of Compliance](#))

Product Highlights:

- ? Housing
- ? 2.54 mm Centerline
- ? Connector Type = Slimline
- ? Number of Positions = 22
- ? Number of Rows = Single

[View all Features](#) | [Find Similar Products](#)

Quick Links

[Check Pricing & Availability](#)

[Search for Tooling](#)

[View Mating Products \(12\)](#)

[View Contacts \(19\)](#)

[Product Feature Selector](#)

[Contact Us About This Product](#)

Documentation & Additional Information	
Product Drawings: ? HOUSING, RECEPTACLE, FFC (PDF, English) Catalog Pages/Data Sheets: ? None Available Product Specifications: ? None Available Application Specifications: ? None Available Instruction Sheets: ? None Available CAD Files: (CAD Format & Compression Information) ? 2D Drawing (DXF, Version S) ? 3D Model (IGES, Version S) ? 3D Model (STEP, Version S) List all Documents	Additional Information: ? Product Line Information Additional Product Images: ? Typical Application Related Products: ? Tooling ? Mating Products (12) ? Contacts (19)
Product Features (Please use the Product Drawing for all design activity)	
Product Type Features: ? Product Type = Housing ? Connector Type = Slimline ? Number of Positions = 22 ? Mating Type = Receptacle ? Mating Connector Lock = Without ? Mating Polarization = Without ? Mounting Ears = Without ? Flame Retardant = Yes Mechanical Attachment: ? Panel Attachment = Without Body Related Features: ? Centerline (mm [in]) = 2.54 [0.100] ? Number of Rows = Single	Housing Related Features: ? Housing Material = Thermoplastic ? Housing Flammability Rating = UL 94V -0 Industry Standards: ? RoHS/ELV Compliance = RoHS compliant, ELV compliant ? Lead Free Solder Processes = Not relevant for lead free process ? RoHS/ELV Compliance History = Always was RoHS compliant Conditions for Usage: ? Terminate To = FFC Cable Other: ? Brand = AMP