



Have a Question?
Chat with a Product
Information Specialist

What can we help you find?

Home > Products > RF & Coax > Product Feature Selector > Product Details

1-1478400-0 Product Details

Share Print Email

1-1478400-0

TE Internal Number: 1-1478400-0

Active

BNC RF Connectors

Converted to EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Connector - RF
- Plug
- Connector Style = Plug
- Applies To Coaxial Cable
- Coaxial Cable Termination Type = Solder/Clamp

[View all Features](#)

[Add to My Part List](#) [Request Sample](#) [Find Similar Products](#) [Buy Product](#)

Quick Links

- Pricing & Availability
- Search for Tooling
- Product Feature Selector
- Contact Us About This Product

Documentation & Additional Information	
Product Drawings: - BNC STRAIGHT PLUG SOLDER (PS) RG213 50 ohm (TIF, English) Catalog Pages/Data Sheets: - None Available Product Specifications: - None Available Application Specifications: - None Available Instruction Sheets: - GREENPAR RF CONNECTOR CABLE ASSEMBLY INSTRUCTION SHEET (PDF, English) CAD Files: - None Available	Related Products: Tooling
List all Documents	

Product Features (Please use the Product Drawing for all design activity)	
Product Type Features: - Product Type = Connector - RF - Gender = Plug - Grade = Professional - Sealed = No - Isolated = No - Dielectric Material = PTFE - Coupling Nut Material = Brass - Flats Dimension = 16.0 A/F Mechanical Attachment: - Surface Mountable = No - Hardware Included = No - Panel Mount Retention = Without Electrical Characteristics: - Connector Impedance (Ω) = 50 - Frequency = DC - 4 GHz Termination Features: - Coaxial Cable Termination Type = Solder/Clamp Body Features: - Body Style = Straight - Body Material = Brass - Body Plating = Silver - Polarized = No - Gasket Material = White Silicone Rubber	Contact Features: - Center Contact Material = Brass - Center Contact Plating = Silver Housing Features: - Connector Style = Plug Configuration Features: - Coaxial Cable Type (RG/U or Mfg.) = 213, 8A, PSF 1/4M, Raychem 5012A1422, Raychem 5012E1339, Raychem 5012E1632, Raychem EPD 29108Q, Raychem EPD 71535Q, URM 67 - Number of Ports = 1 Industry Standards: - Government/Industry Qualification = No - RoHS/ELV Compliance = RoHS compliant, ELV compliant - Lead Free Solder Processes = Wave solder capable to 260°C, Wave solder capable to 240°C, Wave solder capable to 265°C - RoHS/ELV Compliance History = Converted to comply with RoHS directive Environmental: - Operating Temperature (Max.) (°C) = 165 Conditions for Usage: - Applies To = Coaxial Cable Packaging Features: - Packaging Method = Individual - Packaging Quantity = 50 Other: - Brand = Greenpar

Corporate Information

- About TE
- Investors
- News Room
- Supplier Portal
- Careers
- Terms & Conditions
- Privacy Policy

Quick Links

- Distributor Inventory
- Product Cross Reference
- Documents & Drawings
- Product Compliance Support Center
- Site Map

Customer Support

- Email or Chat With Us
- Find a Phone Number
- Knowledge Base
- Manage Your Account

Keep Me Informed

