


3-5102935 -6 Product Details

Live Product Chat US Only
8:30am - 5pm ET, Mon - Fri



3-5102935 -6

[Active](#)

.125 inch AMPMODU Level V

[Always EU RoHS/ELV Compliant](#) ([Statement of Compliance](#))

Product Highlights:

- ? Receptacle Assembly
- ? Number of Positions = 40
- ? Number of Rows = Dual
- ? Terminate To Wire
- ? 3.18 x 3.18 mm Centerline, Matrix

[View all Features](#) | [Find Similar Products](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- ? [RECEPTACLE ASSY, LEVEL V DOUBLE ROW, .125 x .125 CL ...](#)
(PDF, English)

Catalog Pages/Data Sheets:

- ? None Available

Product Specifications:

- ? None Available

Application Specifications:

- ? None Available

Instruction Sheets:

- ? None Available

CAD Files: ([CAD Format & Compression Information](#))

- ? [2D Drawing](#) (DXF, Version D)
- ? [3D Model](#) (IGES, Version D)
- ? [3D Model](#) (STEP, Version D)

[List all Documents](#)

Additional Information:

- ? [Product Line Information](#)

Related Products:

- ? [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- ? [Product Type](#) = Receptacle Assembly
- ? [Number of Positions](#) = 40
- ? Wire Termination Type = Insulation Displacement Crimp (IDC)
- ? Stamped = Yes
- ? Color = Black
- ? Comment = White ink stamped, one side with AMP, part no., date code and arrow.

Termination Related Features:

- ? Solder Tail Contact Plating = Tin

Body Related Features:

- ? [Number of Rows](#) = Dual
- ? [Centerline, Matrix \(mm \[in\]\)](#) = 3.18 x 3.18 [.125 x .125]
- ? [Wire Range \(mm \[AWG\]\)](#) = 0.12 -0.40² [26-22]

Contact Related Features:

- ? [Contact Type](#) = Level V (IDC)
- ? [Contact Mating Area Plating Material](#) = Gold (50)
- ? Tandem Style Contact = Without
- ? Contact Material = Copper Alloy

Housing Related Features:

- ? Housing Material = Thermoplastic

Industry Standards:

- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Not relevant for lead free process
- ? RoHS/ELV Compliance History = Always was RoHS compliant

Conditions for Usage:

- ? Terminate To = Wire

Other:

- ? Brand = AMP