

4MM^2,1 IN 2 OUT SPRING TERMINAL BLOCK



✓ ACTIVE

[Buchanan](#) | [Din Rail Terminal Block Systems](#)

TE Part # **2271560-2**

TE Internal #: **2271560-2**

Terminal Block Type : **Spring Terminal Block**

Block Type : **Standard**

Connector System : **Cable-to-Cable**

Number of Positions : **1**

Centerline (Pitch) : **6.15 mm [.242 in]**

[Add to List](#) ▾

[Similar Products](#)

[ORDER SAMPLES](#)

[Compatible Parts & Tooling](#)

SHOP OUR DISTRIBUTORS

North America ▾

Request pricing, availability and customization options

[CONTACT US](#)

We are here to help!

Get in touch with our product experts.

[CHAT WITH US](#)

[EMAIL US](#)

[CALL US](#)

DOCUMENTS

FEATURES

PRODUCT COMPLIANCE

Product Drawings

4MM^2,1 IN 2 OUT SPRING TERMINAL BLOCK

[4MM^2,1 IN 2 OUT SPRING TERMINAL BLOCK](#)

English

CAD Files

3D PDF

[3D_CVM_CVM_2271560-2_A.pdf](#) 3D

Customer View Model

[ENG_CVM_CVM_2271560-2_A.2d_dxf.zip](#)

English

[ENG_CVM_CVM_2271560-2_A.3d_igs.zip](#)

English

[ENG_CVM_CVM_2271560-2_A.3d_stp.zip](#)

English

Product Specifications

Application Specification

[ENG_SS_114-137138_A3.pdf](#) English

Product Specification

[ENG_SS_108-137138_A3.pdf](#) English

Please review product documents or [contact us](#) for the latest agency approval information. Please Note: Use the Product Drawing for all design activity.



Product Type Features

Terminal Block Type : **Spring Terminal Block**

Block Type : **Standard**

Connector System : **Cable-to-Cable**

Sealable : **No**

Product Type : **Terminal Block**

Configuration Features

Number of Positions : **1**

Number of Circuits : **2**

Ground Function : **Without**

Fuse Function : **Without**

Switch Function : **Without**

Number of Contacts : **1**

Electrical Characteristics

Current Rating (A): **30**

Voltage Rating (VAC): **600**

Continuous Current Rating (A):
30

Contact Features

Contact Base Material : **Copper**

Contact Configuration : **Quick Connect**

Contact Current Rating (Max) (A):
30

Contact Plating Material : **Matte Tin**

Mechanical Attachment

Connector Mounting Type :
DIN Rail

Housing Features

Centerline (Pitch) : **6.15 mm [.242 in]**

Housing Color : **Blue**

Housing Material : **Nylon**

Dimensions

Wire Size : **28 – 10 AWG [.08 – 4 kcmil]**

Usage Conditions

Operating Temperature Range (°C):
-40 – 105

Operation/Application Circuit Application : **Power**

Industry Standards

UL Flammability Rating : **UL 94V-0**

Statement of
Compliance

[Statement of Compliance pdf](#)

Compatible Parts

[> Contact Product Support](#)

Also in the Series | [Din Rail Terminal Block Systems](#)



Terminal Block
Hardware (26)




Terminal Block
Marking (4)




Terminal Blocks (158)


Customers Also Bought




TE Part # 68085
DIE COPALUM IP
69099 6



TE Part # 52746
SPLICE, COPALUM
PARA 6



TE Part # 52791
SPLICE, COPALUM
PARA 16-14



TE Part # 52792
SPLICE, COPALUM
PARA 12-10