

2.5MM^2,1 IN 2 OUT SPRING TERMINAL BLOCK

✓ ACTIVE

[Buchanan](#) | [Din Rail Terminal Block Systems](#)

TE Part # **2271556-3**

TE Internal #: **2271556-3**

Terminal Block Type : **Spring Terminal Block**

Block Type : **Standard**

Connector System : **Cable-to-Cable**

Number of Positions : **1**

Centerline (Pitch) : **5.15 mm [.202 in]**


[Add to List](#) ▾

[Similar Products](#)



ORDER SAMPLES

[Compatible Parts & Tooling](#)



SHOP OUR DISTRIBUTORS

North America ▾

Request pricing, availability and customization options

[CONTACT US](#)



We are here to help!

Get in touch with our product experts.



[CHAT WITH US](#)



[EMAIL US](#)



[CALL US](#)

DOCUMENTS

FEATURES

PRODUCT COMPLIANCE

Product Drawings

2.5MM^2,1 IN 2 OUT SPRING TERMINAL BLOCK

[2.5MM^2,1 IN 2 OUT SPRING TERMINAL BLOCK](#)

English

CAD Files

3D PDF

[3D_CVM_CVM_2271556-3_A.pdf](#) 3D

Customer View Model

[ENG_CVM_CVM_2271556-3_A.2d_dxf.zip](#)

English

[ENG_CVM_CVM_2271556-3_A.3d_igs.zip](#)

English

[ENG_CVM_CVM_2271556-3_A.3d_stp.zip](#)

English

Product Specifications

Application Specification

[ENG_SS_114-137138_A3.pdf](#) English

Product Specification

[ENG_SS_108-137138_A3.pdf](#) English

Please review product documents or [contact us](#) for the latest agency approval information. Please Note: Use the Product Drawing for all design activity.



Product Type Features

Terminal Block Type : **Spring Terminal Block**

Block Type : **Standard**

Connector System : **Cable-to-Cable**

Sealable : **No**

Product Type : **Terminal Block**

Configuration Features

Number of Positions : **1**

Number of Circuits : **2**

Ground Function : **Without**

Fuse Function : **Without**

Switch Function : **Without**

Number of Contacts : **1**

Electrical Characteristics

Current Rating (A): **20**

Voltage Rating (VAC): **600**

Continuous Current Rating (A):
20

Contact Features

Contact Base Material : **Copper**

Contact Configuration : **Quick Connect**

Contact Current Rating (Max) (A):
20

Contact Plating Material : **Matte Tin**

Mechanical Attachment

Connector Mounting Type :
DIN Rail

Housing Features

Centerline (Pitch) : **5.15 mm [.202 in]**

Housing Color : **Orange**

Housing Material : **Nylon**

Dimensions

Wire Size : **28 – 12 AWG [.08 – 2.5 kcmil]**

Usage Conditions

Operating Temperature Range (°C):
-40 – 105

Operation/Application Circuit Application : **Power**

Industry Standards

UL Flammability Rating : **UL 94V-0**

Statement of Compliance

[Statement of Compliance pdf](#)

Compatible Parts

[> Contact Product Support](#)

Also in the Series | [Din Rail Terminal Block Systems](#)



[Terminal Block Hardware \(26\)](#)




[Terminal Block Marking \(4\)](#)



[Terminal Blocks \(158\)](#)

Customers Also Bought



TE Part # 68085
DIE COPALUM IP
69099 6



TE Part # 52746
SPLICE, COPALUM
PARA 6



TE Part # 52791
SPLICE, COPALUM
PARA 16-14



TE Part # 52792
SPLICE, COPALUM
PARA 12-10

[About TE Connectivity](#)

[For Partners](#)

[Customer Support](#)

CALL US

LIVE CHAT

[United States](#)

[Our Company](#)

[Events](#)

[TE News Center](#)

[Careers](#)


[Investors](#)

[Corporate Responsibility](#)

[Terms and Conditions of Sale](#)

[Distributors](#)

[Suppliers](#)

 [Email or Call Us](#)

 [Find Authorized Distributors](#)

 [What's New on TE.com](#)

 [Product FAQs](#)

[Select Country & Language](#)

[United States \(EN\)](#)

[Germany \(DE\)](#)

[China \(中文\)](#)

[Japan \(日本語\)](#)

[Find Your Country/Region](#) ▼