

Products

Documentation

Resources


My Account

Customer Support

5650936

- 5

Product Details



5650936

- 5

Active

Eurocard Type R

Always EU RoHS/ELV Compliant

(

Statement of Compliance

)

Product Highlights:

- ? Plug
- ? Number of Positions = 32
- ? PCB Mount Angle = Vertical
- ? No PCB Retention Feature
- ? Post Type = Solder Post

View all Features

|

Find Similar Products

Live Product Chat

US Only

8:30am - 5pm ET, Mon - Fri

Quick Links

- Check Pricing & Availability

Search for Tooling

View Mating Products (1)

Product Feature Selector

Contact Us About This Product

Documentation & Additional Information	
Product Drawings: ? ASSEMBLY, PIN, EUROCARD, TYPE 1/2R, A and C, 32/48 P... (PDF, English) Catalog Pages/Data Sheets: ? None Available Product Specifications: ? None Available Application Specifications: ? Eurocard Connectors Types B,C,M,Q,R. & Enchanced Typ... (PDF, English) Instruction Sheets: ? None Available CAD Files: ? None Available List all Documents	Additional Information: ? Product Line Information Related Products: ? Tooling ? Mating Products (1)

Product Features (Please use the Product Drawing for all design activity)	
Product Type Features: ? Product Type = Plug ? Number of Positions = 32 ? PCB Mount Angle = Vertical ? PCB Retention Feature = No ? Post Type = Solder Post ? Mating Polarization = Without ? Guides = Without ? Make First / Break Last = No ? DIN Level = II ? Color = Gray Termination Related Features: ? Termination (Solder) Post Length (mm [in]) = 4.57 [0.180] ? Solder Tail Contact Plating = Tin Body Related Features: ? Rows Loaded = A, C ? Contact Cross Section (mm [in]) = 0.64 [.025] Sq.	Contact Related Features: ? Contact Material = Copper Alloy ? Contact Mating Area Plating = DIN 41612 Class 2 Housing Related Features: ? Housing Material = Polymer ? Housing Flammability Rating = UL 94V -0 Industry Standards: ? RoHS/ELV Compliance = RoHS compliant, ELV compliant ? Lead Free Solder Processes = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C ? Flux - Tight Coating = Without ? RoHS/ELV Compliance History = Always was RoHS compliant Other: ? Brand = AMP