



+ CONNECTORS

TERMINAL BLOCKS



✓ Active

TE CONNECTIVITY (TE)

16MM², SPRING PE TYPE TERMINAL BLOCK

2271592-1

TE Internal Number: 2271592-1

[EU RoHS Compliant](#)

[EU ELV Compliant](#)

Terminal Block Type Spring Terminal Block

Centerline (Pitch) 12.2 mm [.48 in]

Operating Temperature Range (°C) -40 – 105

Connector Mounting Type DIN Rail

Block Type Standard



PRODUCT DRAWING

English

DOCUMENTATION

Product Drawings

16mm², 1 In And 1 Out Spring Clamp Type Terminal Block

PDF

English

16mm², 1 In And 1 Out Spring Clamp Ground Type Terminal Block

PDF

English

Product Specifications

Product Specification

Product Specification For Din Rail Type Spring Terminal Block With Ground Function

PDF

English

Application Specification

Application Specification For Spring Terminal Block Connectors

PDF

English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Terminal Block Type Spring Terminal Block

Block Type Standard

Product Type Terminal Block

Configuration Features

Number of Circuits 1

Ground Function With

Fuse Function Without

Switch Function Without

Number of Contacts 1

Electrical Characteristics

Voltage Rating (VAC) 600

Contact Features

Contact Configuration Quick Connect

Contact Plating Material Matte Tin

Contact Base Material Copper

Mechanical Attachment

Connector Mounting Type DIN Rail

Housing Features

Centerline (Pitch) 12.2 mm [.48 in]

Housing Color Green

Housing Material Nylon

Dimensions

Wire Size 24 – 4 AWG [.2 – 16 kcmil]

Usage Conditions

Operating Temperature Range (°C) -40 – 105

Industry Standards

UL Flammability Rating UL 94V-0

Statement of Compliance

Statement of Compliance

PDF