

Product: [5400UE](#)

Security & Sound, 2 Conductor 20 AWG, BC, Unshielded, CMR



## Product Description

Security & Commercial Audio Cable, Riser-CMR, 2-20 AWG stranded bare copper conductors with polyolefin insulation, PVC jacket with ripcord

## Technical Specifications

### Product Overview

Suitable Applications:	Security Systems, Intercom/PA Systems, Sound/Audio Systems, Power Limited Controls, Single Line Telephone
------------------------	---

### Physical Characteristics (Overall)

#### Conductor

AWG	Stranding	Material	No. of Conductors
20	7x28	BC - Bare Copper	2

Conductor Count:	2
------------------	---

#### Insulation

Material	Nominal Wall Thickness
PP - Polypropylene	0.008 in

#### Color Chart

Number	Color
1	Black
2	Red

#### Outer Shield Material

Material
No Shield

#### Outer Jacket Material

Material	Nominal Diameter	Nominal Wall Thickness	Ripcord
PVC - Polyvinyl Chloride	0.138 in	0.017 in	Yes

### Construction and Dimensions

#### Cabling

Twists
4 twist/ft

### Electrical Characteristics

#### Conductor DCR

Nominal Conductor DCR
10.2 Ohm/1000ft

#### Capacitance

Nom. Capacitance Conductor to Conductor
18.5 pF/ft

## Inductance

### Nominal Inductance

0.18 µH/ft

## Current

### Max. Recommended Current [A]

3.75 Amps per Conductor at 25°C

## Voltage

### UL Voltage Rating

300 V RMS

## Temperature Range

UL Temp Rating:	75°C
Operating Temp Range:	-20°C To +75°C

## Mechanical Characteristics

Bulk Cable Weight:	12 lbs/1000ft
Max. Pull Tension:	25.2 lbs
Min Bend Radius/Minor Axis:	1.375 in

## Standards

NEC Articles:	Article 800
NEC/(UL) Compliance:	CMR
CEC/C(UL) Compliance:	CMG
CPR Euroclass:	Eca

## Applicable Environmental and Other Programs

Environmental Space:	Indoor - Riser
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2005-04-01
MII Order #39 (China RoHS):	Yes

## Flammability, LS0H, Toxicity Testing

C(UL) Flammability:	FT4
UL Flammability:	UL1666 Vertical Shaft
IEC Flammability:	IEC 60332-1-2
UL voltage rating:	300 V RMS

## Plenum/Non-Plenum

Plenum (Y/N):	No
Plenum Number:	6400UE

## Part Number

### Variants

Item #	Color	Putup Type	Length	UPC
5400UE 0081000	Gray	Reel	1,000 ft	612825161981
5400UE 008U1000	Gray	UnReel	1,000 ft	612825420101
5400UE 008Z1000	Gray	ReelTuff Box	1,000 ft	612825162018

Footnote: C - CRATE REEL PUT-UP.

## History

Update and Revision:	Revision Number: 0.270 Revision Date: 06-24-2020
----------------------	--

© 2020 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.