




CONNECTOR HOUSINGS



✓ Active

TE CONNECTIVITY (TE) POWER DBL LOCK CAP P/M 3P(GWT)

Power-Signal Double Lock | Power Double Lock

5-177907-1
 TE Internal Number: 5-177907-1

- Always EU RoHS/ELV Compliant
- Connector System **Wire-to-Panel, Wire-to-Wire**
- Centerline **3.96 mm [.156 in]**
- Number of Positions **3**
- Number of Rows **1**
- Housing Material **Nylon 6/6**

No documentation available.

Please review product documents or [contact us](#) for the latest agency approval information.

Product Type Features	Connector System	Wire-to-Panel, Wire-to-Wire
	Connector Style	Receptacle
	Sealed	No
	Applies To	Panel, Wire/Cable
	Product Type	Connector
	Connector Type	Housing
Configuration Features	Number of Positions	3
	Number of Rows	1
	Selectively Loaded	No
	Preloaded	No
Electrical Characteristics	Operating Voltage (VAC)	300
Body Features	Sealable	No
Contact Features	Contact Type	Tab

	Shunts/Shorting Bars	Without
	Multiple Contact Types	Without
Mechanical Attachment	Contact Retention	Without
Housing Features	Centerline	3.96 mm [.156 in]
	Housing Material	Nylon 6/6
	Housing Color	Natural
Dimensions	Length (mm)	13.9
	Height	26.1 mm [1.02 in]
	Width (mm)	9.4
Usage Conditions	Operating Temperature Range	-30 – 105 °C [-22 – 221 °F]
Operation/Application	Assembly Integration Feature	Without
Identification Marking	Circuit Identification Feature	Without
Industry Standards	CSA Rating	Certified
	CSA File Number	LR7189
	UL Rating	Recognized
	CSA Certified	Yes
	VDE Tested	Yes
	UL File Number	E28476
Packaging Features	Packaging Quantity	150
	Packaging Method	Bag
Product Compliance	Statement of Compliance PDF	VIEW ALL PRODUCT COMPLIANCE