




CONNECTORS

MULTIPLE CONFIGURATION PCB HEADERS & RECEPTACLES



✓ Active

TE CONNECTIVITY (TE)

1P AMPMODU II PIN HDR

AMPMODU | AMPMODU Headers

826632-1

TE Internal Number: 826632-1

EU RoHS Compliant

EU ELV Compliant

Connector Style Plug

Sealable No

Centerline (mm) 2.54

Centerline (Pitch) (in) .1

Header Type Breakaway

↓ **PRODUCT DRAWING**
English

↓ **3D PDF**

DOCUMENTATION

Product Drawings

AMPMODU II STIFTLISTE ZWEIREIHIG

PDF

English

CAD Files

Customer View Model

2D_DXF.ZIP

English

Customer View Model

3D_IGS.ZIP

English

Customer View Model

3D_STP.ZIP

English

3D PDF

PDF

English

Agency Approvals

Agency Approval Document

AMPMODU CONNECTOR REPORT (GERMANY)

PDF

English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Connector Style Plug

Sealable No

PCB Mounting Orientation Vertical

Connector Type Header

Row-to-Row Spacing 2.54 mm [.1 in]

Profile Standard

Product Type Connector

Board Standoff With

Strain Relief Without

Configuration Features

Number of Rows 2

Selectively Loaded No

Staggered Rows No

Keyed No

Body Features

Header Type Breakaway

Post Size .64 mm [.025 in]

Contact Features

Contact Base Material CuZn

Underplate Material Nickel

Contact Type Pin

Contact Mating Area Plating Thickness (µin) 30

Contact Mating Area Plating Material Gold Flash over Palladium Nickel

Solder Tail Contact Plating Material Tin over Nickel

Contact Shape Square

Termination Features

Termination Post Length 3.2 mm [.126 in]
Contact Termination Type Through Hole
Termination Method to PC Board Through Hole
Termination End Plating Material Tin over Nickel

Mechanical Attachment

PCB Mounting Style Through Hole-Solder
PCB Mount Retention Without
Mating Alignment Without
Panel Mount Retention Without
Mating Connector Lock Without

Housing Features

Centerline (mm) 2.54
Centerline (Pitch) (in) .1
Housing Material PBT GF
Housing Color Green

Dimensions

Mating Post Length 6.7 mm [.264 in]

Usage Conditions

High Temperature Housing No

Operation/Application

High Speed Serial Data Connector No

Industry Standards

UL Flammability Rating UL 94V-0

Packaging Features

Packaging Quantity 3000
Packaging Method Box

Statement of Compliance

Statement of Compliance

PDF
