

TE Part Number: 1393781-5



Superseded

[Add to Part List](#)
[Search for Replacement
Parts](#)

 Converted to EU RoHS/ELV Compliant (Statement of Compliance)

- V23111 Series
- Contact Arrangement = 1 Form C, SPDT, 1 C/O
- Contact Current Rating = 1 Amps.
- Monostable Coil Magnetic System
- Without Coil Suppression Diode

[View all Features](#) | [Find Similar Products](#)

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

Product Drawings:

- None Available

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- Product Line Information

Additional Product Images:

- Schematic
- PCB Layout
- Wiring Diagram

Related Products:

- Tooling

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Termination Type = Through Hole

Electrical Characteristics:

- Contact Current Rating (Amps.) = 1
- Coil Resistance (Ω) = 960
- Coil Power, Nominal (mW) = 150
- Actuating System = DC
- Input Voltage (VDC) = 12
- Coil Rating = Sensitive

Body Related Features:

- Series = V23111
- Polarized = No

Contact Related Features:

- Mounting Options = PC Board
- Enclosure = Sealed
- FCC Part 68 Isolation = Yes
- Relay Type = PCB
- Contact Material = Silver Nickel, Gold Plated
- Approx. Dimensions (L x W x H) (mm [in]) = 12.50 x 7.50 x 10.00 [.492 x .295 x .394]
- Wiring Diagram = 1 Form C
- Approved Standards = UL Recognized, CSA Certified

Configuration Related Features:

- Contact Arrangement = 1 Form C, SPDT, 1 C/O
- Coil Magnetic System = Monostable
- Coil Suppression Diode = Without
- Coil Selection Criteria = Nominal Voltage
- Coil Latching = Without
- LED Indicator = Without

Industry Standards:

- RoHS/ELV Compliance = RoHS compliant, ELV compliant
- Lead Free Solder Processes = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- RoHS/ELV Compliance History = Converted to comply with RoHS directive

Other:

- Brand = Potter & Brumfield