



Connectors > Automotive, Truck, Bus, & Off-Road Connectors > Connector Accessories > Connector Caps & Covers



Accessory Type: **Cover - Cable Exit**

Cable Exit Angle: **180 (In-Line)**

Strain Relief: **Without**

Color: **Black**

Material: **PA**

Features

Product Type Features

Accessory Type	Cover - Cable Exit
Strain Relief	Without

Configuration Features

Number of Positions	2
---------------------	---

Body Features

Cable Exit Angle	180 (In-Line)
Color	Black
Material	PA

Usage Conditions

Operating Temperature Range	-40 – 150 °C[-40 – 302 °F]
-----------------------------	----------------------------

Packaging Features

Packaging Method	Bulk
Packaging Quantity	1

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2020 (205) Candidate List Declared Against: JAN 2020 (205) Does not contain REACH SVHC
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2020 (205) Candidate List Declared Against: JAN 2020 (205)
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.


Compatible Parts



Also in the Series | [MCON Interconnection System](#)



Automotive Connector Caps & Covers (24)



Automotive Connector Locks & Position Assurance(11)



Automotive Seals & Cavity Plugs(4)



Automotive, Truck, Bus, & Off-Road Headers(5)



Automotive, Truck, Bus, & Off-Road Housings(285)



Automotive, Truck, Bus, & Off-Road Terminals(113)



Other Automotive Connector Accessories(6)

Customers Also Bought



TE Model / Part #2151042-1
OCEAN_2.0_APPLICATOR-S-050F070O



TE Model / Part #7-2151068-7
OCEAN_2.0_SPARE_PART_KIT-062F072O



TE Model / Part #2292906-2
2POS,MCON 1.2,REC HSG ASSY,SLD,COD B



TE Model / Part #2292906-1
2POS,MCON 1.2,REC HSG ASSY,SLD,COD A



TE Model / Part #2272976-3
Right Angle Wire Dress



TE Model / Part #2272162-1
MCON WIRE DRESS, 4P, STRAIGHT



TE Model / Part #2272164-1
MCON WIRE DRESS, 3P, STRAIGHT



TE Model / Part #2304518-1
MCON 1.2CB SEAL CAVITY PLUG, EXTRA LONG

Documents

Product Drawings

MCON WIRE DRESS, 2P PLUG, STRAIGHT

English

CAD Files

3D PDF

3D

Customer View Model



[ENG_CVM_CVM_2272168-1_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2272168-1_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2272168-1_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English