

SCFRF902AA Product Details



SCFRF902AA

TE Part Number: 1437464-8

✓ **Active**

[Add to Part List](#)

Time Delay Relays

[Not EU RoHS or ELV Compliant](#)

Product Highlights:

- SCF Multi-Mode, Multi-Range Timer Series
- Time Delay Relay
- Input Voltage = 120 VAC
- Input Voltage = 125 VDC
- Contact Arrangement = 2 Form C, DPDT, 2 C/O

[View all Features](#) | [Find Similar Products](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)
- ▶ [Request Samples](#)

NEW!

Documentation & Additional Information

Product Drawings:

- None Available

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Product Type = Time Delay Relay
- Termination Type = 11-Pin Octal Style Plug
- Comment = Does not include socket.

Electrical Characteristics:

- Input Voltage (VAC) = 120
- Input Voltage (VDC) = 125
- Contact Rating = 10A Resistive @ 28 VDC/120 VAC

Body Related Features:

- [Series](#) = SCF Multi-Mode, Multi-Range Timer

Contact Related Features:

- Mounting Options = Socket
- Mode of Operation = Interval, Latching Interval, Off-Delay, On-Delay
- Delay Time = 0.1 seconds to 3 seconds, 0.33 seconds to 10 seconds, 0.33 minutes to 10 minutes, 0.33 hours to 10 hours, 1 minute to 30 minutes, 1 second to 30 seconds, 2 minutes to 60 minutes, 4 seconds to 120 seconds
- Type of Control = Screw
- Repeatability, Max. = ±1% ±10 msec
- Approved Standards = CE Approved, CSA Certified, UL Recognized
- Option = With Socket
- Approx. Dimensions (L x W x H) (mm [in]) = 72.00 x 36.00 x 90.00 [2.836 x 1.418 x 3.546]

Configuration Related Features:

- [Contact Arrangement](#) = 2 Form C, DPDT, 2 C/O
- Multiple Timing Ranges = Without

Industry Standards:

- [RoHS/ELV Compliance](#) = Not ELV/RoHS compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process

Conditions for Usage:

- Temperature Range (°C) = -30 - +65

Other:

- Brand = Agastat