





LOC	DIST	REVISIONS					
		P.	LTN	DESCRIPTION	DATE	DWN	APVD
		1		INITIAL DRAWING	30MAR2012	AD	AD
		2		ORG W/RED WAS RED, ORG W/BLK WAS BLK	30MAY2012	AD	AD
		3		ADD NOTE 4	07SEP2012	AD	AD



- △ ALL TERMINALS MUST BE FULLY SEATED AND LOCKED IN POSITION TWO PLACES PER TERMINAL
- △ SEAL MUST BE FULLY SEATED TO ENSURE RETENTION DURING SHIPPING AND HANDLING
- △ ALL COMPRESSION LIMITERS MUST BE FULLY SEATED 4 PLCS
- △ SEE THE FOLLOWING SPECIFICATIONS:
 408-10441 CONNECTOR INSTRUCTION SHEETS
 114-18051-1 TERMINAL APPLICATION SPECIFICATION
 114-18021 TERMINAL APPLICATION SPECIFICATION

QTY	PART NO.	DESCRIPTION	ITEM NO
AR	-	4.0mm SQ. CABLE, ORANGE W/BLACK STRIPE	6
AR	-	4.0mm SQ. CABLE, ORANGE W/RED STRIPE	5
AR	-	0.5mm SQ. WIRE, BLACK	4
2	963715-6	MOS 0.65 TERMINAL RECEPTACLE	3
2	2-2141600-2	MCP 2.8 TERMINAL BLADE	2
1	2103124-1	HEADER SUBASSY, KEY A	1
PARTS LIST			

THIS PRINT IS
PRELIMINARY
 UNQUALIFIED PRODUCT
 CONTACT PRODUCT ENGINEERING
 BEFORE USING THIS PRINT

THIS PRODUCT HAS NOT COMPLETED VALIDATION TESTING

THIS DRAWING IS A CONTROLLED DOCUMENT. DIMENSIONING AND TOLERANCING PER ASME Y14.5M-2009.		DWN: A DECHAZAL 30MAR2012	CHG: D SIMPSON 30MAR2012	APVD: 30MAR2012
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	PRODUCT SPEC: -		
0 PLC ±0.5	1 PLC ±0.10	APPLICATION SPEC: △		
2 PLC ±0.13	3 PLC ±0.0001	MATERIAL: -		
4 PLC ±0.0001	ANGLES ±0.0001	FINISH: -		
CUSTOMER DRAWING		WEIGHT: -	SIZE: A1	CAGE CODE: 2103333
SCALE: 2:1		SHEET: 1 OF 1		REV: 3

STE TE Connectivity
 PRELIMINARY
 HEADER PLCTAIL ASSY
 HVA280-2PHX HEADER