




Switches > Tactile Switches



Actuator Style: **Rectangular Actuator**
Operating Function: **NO**
Contact Base Material: **Copper Alloy**
Switch Contact Plating Material: **Silver**
Low Profile: **With**

Features

Product Type Features

Leg Style	J Style
Switch Connection Type	Printed Circuit Board
Illuminated	With
Actuator Style	Rectangular Actuator

Configuration Features

Switch Feedback Type	Tactile
ESD Grounding Terminal	Without
Ganged	With
Operating Function	NO
Support Bracket	Without
Configuration (Pole-Throw)	Single Pole - Single Throw
Number of Actuators	Single

Electrical Characteristics

Operating Voltage	24 VDC
-------------------	--------



Body Features

Case Material	PPS
Actuator Profile	Extended
Case Color	Brown
Actuator Material	PPS
Cover Material	Stainless Steel
Actuator Force	180 g[6.34 oz]
Product Orientation	Vertical
Actuator Color	Black

Contact Features

Contact Base Material	Copper Alloy
Switch Contact Plating Material	Silver
Contact Current Rating	50 mA

Termination Features

Termination Method to PCB	Surface Mount
---------------------------	---------------

Housing Features

Low Profile	With
Process Sealed	No

Dimensions

Button Width	3 mm[.11 in]
Product Height	5 mm[.196 in]
Actuator Length	1.5 mm[.059 in]

Usage Conditions

Operating Temperature Range	-35 – 85 °C[-31 – 185 °F]
-----------------------------	---------------------------

Packaging Features

Packaging Method	Tape & Reel
------------------	-------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted




	Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts




TE Part # 3-1437565-0
FSM2JSMATR=ON T/R



TE Part # 2-1825910-7
FSM14JH=6MM TACT SWITCH, HIGH TEMP



TE Part # 4-1437565-2
FSM4JSMATR=TACT SWITCH 6X6MIL



TE Part # 1825910-6
FSM4JH=6MM TACT SWITCH, HIGH TEMP



TE Part # 2-1977223-8
FSM14JSMAS=6MM TACT SWITCH, SMT 160gf

Customers Also Bought





TE Part #HUM-900-PRC-CAS
Module HUM-PRC 900MHz FHSS FM XCVR FCC



TE Part #HUM-868-PRC-CAS
Module HUM-PRC 868MHz FHSS FM XCVR EU



TE Part #1-1614885-6
CPF 0805 330K 0.1% 25PPM 1K RL




TE Part #5-1614893-5
CPF 0805 49K9 0.1% 25PPM 1K RL




TE Part #1622378-1
LR1 1% 1R8



TE Part #2-2176058-0
RLP73N 3A R062 5% 2K RL



TE Part #2314867-5
5P,2MM,BB,REC,SRVT,2.0,SN,TUBE W /CAP



TE Part #2-2176315-2
MELF SMA_A 5K6 0.1% 15PPM 0204 0.4W



TE Part #ANT-868-USP-T
Antenna uSP PCB RPC 868MHz SMT T&R



TE Part #1SNA116523R0000
BFU2.S6.G

Documents

Product Drawings

SWITCH,TACT,SMT,J-LEAD,5.0MM

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_147873-1_K_c-147873-1-k.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_147873-1_K_c-147873-1-k.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_147873-1_K_c-147873-1-k.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Datasheets & Catalog Pages



SWITCHES_CORE_PROGRAM_CATALOG

English

Products for Mobile Equipment

English

Tactile Switches

English

8-1773450-9_SWITCHES_CATALOG_SECTION_C_TACTILE_SWITCHES

English