








SYMBOL DEFINITION		MISSING NUMBERS	
A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL  DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON AN INDIVIDUAL COMPONENT DRAWING.	TOTAL NO. OF SYMBOLS ON DRAWING	15	25-26,
	LAST NO. USED	30	


DWG STATUS					ZONE	REVISION HISTORY	AUTH	DR	APD	APD	
DATE	STG	REV	N/P	CHG						1	2
04N099	R	001	-	-		CLARED REVISION COLUMN: ALL PARTS - REVISED GRAPHICS	197500	PHC	JGS	MC	
03JA00	R	002	-	-		ALL PARTS REVISED, (19.4) WAS 19.4	198070	JHH	JHH	MC	M
27MR00	R	003	-	-		ALL PARTS - REVISED PLR	199420	KBD	KBD	MC	
20AP00	R	004	-	-		ALL PARTS - ADDED (12.8) DIM & REMOVED 30.6 & 30.6 DIMS	199528	EVV	MVA	MC	
29MR01	R	005	-	-		ALL PARTS - REVISED NOTES	206589	KBD	KBD	MJC	
29MR01	R	006	-	-		15397579 - RELEASED	207607	KBD	KBD	MJC	
22FE02	R	007	-	-		ALL PARTS - ADDED TPA MATING PART INFORMATION	220843	EVV	EVV	AH	
13JA04	R	08	-	-		ADDED 15485648 AND REVISED NOTE 3	249215	BRB	BRB	LN	L
13JA04	R	08	-	-		ADDED 15487755	250452	BRB	BRB	LN	
06MY04	R	09	-	-		CORRECTED ASSEMBLIES - 15326820, 15485648, 15487755.	254724	LLJ	LLJ	LN	
10AU04	R	10	-	-		ALL PARTS - ADDED CAVITY PLUG NOTE; ADDED PART 13510099	257917	RH	RH	LN	
01DE04	R	11	-	-		15326806 - UPDATED PDM ATTRIBUTES	261604	HAM	HAM	MJC	
04JA05	R	12	-	-		13519049, 13519053 - RELEASED	262679	ADK	ADK	LN	
07FE05	R	13	-	-		13519592 - RELEASED	264260	JPB	JVM	PYP	
29JN05	R	14	-	-		RELEASED 13533785	269268	JEB	JEB	LN	
180C05	R	15	-	-		ALL PARTS - ADDED "CONN COLOR" COLUMN TO CHART: 15326806, 15326827 & 15326820 - CHANGED STATUS TO RESTRICTED AND ADDED "REPLACED BY" PART NUMBER: 13519592 - OBSOLETE: 13546698 - RELEASED	273303	CJP	CJP	LN	K
13FE06	R	16	-	-		UPDATED PDM ATTRIBUTES	277480	TS	TS	SM	
17AP06	R	17	-	-		13510099 - UPDATED PDM ATTRIBUTES	279594	JBD	AUG	SRM	



NOTES

- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED: DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION. (SEE MATH MODEL FOR PRECISE DIMENSIONS.) FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
- MATING COMPONENTS OR EQUIVALENT: PLASTIC MATING ASSEMBLY PARTS SEE CHART
- THIS PART ACCEPTS THE FOLLOWING COMPONENTS OR EQUIVALENT:
TERMINAL 15326268
CABLE SEAL 15366021
CAVITY PLUG 15305171
METAL CLIP SEE TAXI 08900009
PLASTIC SELF LOCKING CLIP 15358639

THIS CONNECTOR MEETS OR EXCEEDS SAE/USCAR-2 AUGUST 1997, SECTION 5.3.1.2, TERMINAL DISENGAGE CRITERIA WITH THE APPLICATION OF A TERMINAL POSITION ASSURANCE (TPA) SECONDARY LOCK. (SEE CHART BELOW FOR APPROPRIATE TPA).



PART NO	REV	N/P	STATUS	TYPE	CONNECTOR	CONN COLOR	MATERIAL RECYCLING CODE	PLR	MATING ASM CONN	MATING TPA	REPLACED BY
13546698	01	-	-	102	13546697	NAT	PBT-GF20	15326803 / ID404323	13546696	15355128	-
13533785	01	AA	-	102	13534233	GRA	PBT-GF20	15326803 / ID404323	13533784	15355128	-
13519592	01	AA	OBSOLETE	107	13519591	BLK	PA6-GB20 GF10	15326824 / ID404319	13521746	15418547	-
13519053	01	AA	-	105	13519052	BLK	PBT-GF20	15326824 / ID404319	13519051	15418547	-
13519049	01	AA	-	103	13519048	BLK	PBT-GF20	15326810 / ID404322	13519047	15418545	-
13510099	01	AC	-	102	13510098	BLK	PBT-GF20	15326803 / ID404323	13510085	15355128	-
15487755	01	AC	-	104	15487757	BLK	PBT-GF20	15326817 / ID404321	15487756	15418546	-
15485648	01	AC	-	104	15485650	GRA	PBT-GF20	15326817 / ID404321	15485649	15418546	-
15397579	01	AC	-	106	15397576	BLK	PBT-GF20	15326937 / ID404318	15397577	15317363	-
15326833 / ID404618	03	AE	-	106	15326832 / ID404324	BLK	PA6-GB20 GF10	15326829 / ID404613	15317363	-	-
15326827 / ID404617	03	AE	RESTRICTED	105	15326826 / ID404325	BLK	PA6-GB20 GF10	15326824 / ID404319	15326822 / ID404612	15418547	13519053
15326820 / ID404616	03	AF	RESTRICTED	104	15326819 / ID404326	BLK	PA6-GB20 GF10	15326815 / ID404611	15418546	-	15487755
15326813 / ID404615	03	AE	-	103	15326812 / ID404327	BLK	PA6-GB20 GF10	15326810 / ID404322	15326808 / ID404610	15418545	-
15326806 / ID404614	03	AF	RESTRICTED	102	15326805 / ID404328	BLK	PA6-GB20 GF10	15326803 / ID404323	15326801 / ID404609	15355128	13510099

DIMENSIONAL RANGE (MM)		TOLERANCE UNLESS OTHERWISE SPECIFIED		TOLERANCE UNLESS OTHERWISE SPECIFIED	
FROM	TO	±	±	±	±
> 0	> 30	±0.15	±0.2	±0.3	±0.4
> 30	> 70	±0.2	±0.3	±0.4	±0.5
> 70	> 100	±0.3	±0.4	±0.5	±0.6
> 100	> 150	±0.4	±0.5	±0.6	±0.8
> 150	> 200	±0.5	±0.6	±0.8	±1.0
> 200	> 250	±0.6	±0.8	±1.0	±1.2
> 250	> 300	±0.8	±1.0	±1.2	±1.5

PART DRAWING	
STYLE	DATE
VOLUME (10/1)	DATE
SEE CHART	DATE
UNLESS OTHERWISE SPECIFIED	DATE
THIS DOCUMENT IS IN ACCORDANCE WITH SAE J1454-1994	DATE
AS ISSUED BY THE SAE BOARD OF DIRECTORS AND	DATE
TELEPHONE AND/OR FAX. ALL DIMENSIONS AND	DATE
RELATED DATA APPLY HERE. FILE # (PERFECT FORM AT	DATE
END DOES NOT APPLY HERE RELATIONSHIP BETWEEN FORMS	DATE
IS ESTABLISHED BY ORIGINATOR OR LOCATION TOLERANCES	DATE
SEPARATE POSITION CALLOUTS MAY BE SHOWN SEPARATELY,	DATE
REMARKS OF DATA REFERENCE.	DATE
ALL DIMENSIONS ARE IN MILLIMETERS	DATE

DELPHI	
DELPHI PACKARD ELECTRIC SYSTEMS	
WARREN, MI	
DR	DATE
APVD1 M. MCCALL	16JL97
APVD2 M. MCCALL	16JL97
APVD3 M. CHUPAK	25JL97
APVD4	
APVD5	
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER DELPHI 1044001	
MATERIAL SEE DRAWING	
DRAWING NAME	
TAXI ASM CONN M 6T 150 SLD	
DRAWING NUMBER	
15326962	
SIZE	SCALE
A0	5:1
FRAME NO	SHEET NO
1 OF 2	1 OF 1
REV	N/P
17	-