

## 1227A1 Multi-Conductor - Category 3 Nonbonded-Pair Cable



For more Information  
please call

1-800-Belden1



### Description:

24 AWG solid bare copper conductors, twisted pairs, non-plenum, Polyolefin insulation, see color code chart (below), Gray PVC jacket.

### Physical Characteristics (Overall)

#### Conductor

##### AWG:

# Pairs	AWG	Stranding	Conductor Material
2	24	Solid	BC - Bare Copper

#### Insulation

##### Insulation Material:

Insulation Material
PP - Polypropylene

#### Outer Shield

##### Outer Shield Material:

Outer Shield Material
Unshielded

#### Outer Jacket

##### Outer Jacket Material:

Outer Jacket Material
PVC - Polyvinyl Chloride

#### Overall Cable

Overall Nominal Diameter: 0.173 in.

#### Pair

##### Pair Color Code Chart:

Number	Color
1	White/Blue Stripe & Blue
2	White/Orange Stripe & Orange

### Mechanical Characteristics (Overall)

Operating Temperature Range:	-20°C To +80°C
UL Temperature Rating:	75°C
Bulk Cable Weight:	13 lbs/1000 ft.
Max. Recommended Pulling Tension:	15 lbs.
Min. Bend Radius (Install)/Minor Axis:	0.800 in.

### Applicable Specifications and Agency Compliance (Overall)

#### Applicable Standards & Environmental Programs

NEC/(UL) Specification:	CMR, CMX OUTDOOR, UL444
CEC/C(UL) Specification:	CMR, CMX OUTDOOR
IEEE Specification:	802.3 10BaseT, 100BaseT4
EU CE Mark:	Yes

## 1227A1 Multi-Conductor - Category 3 Nonbonded-Pair Cable

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	01/01/2004
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes
Telecommunications Standards:	568-B.2 Category 3
Other Specification:	NEMA WC-63 Category 3, UL verified to TIA/EIA-568-B.2, Category 3

### Flame Test

UL Flame Test:	UL1666 Riser
CSA Flame Test:	FT4

### Suitability

Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes
Sunlight Resistance:	Yes

### Plenum/Non-Plenum

Plenum (Y/N):	No
Plenum Number:	1243A2

## Electrical Characteristics (Overall)

### Nom. Mutual Capacitance:

Capacitance (pF/ft)  
15

Maximum Capacitance Unbalance (pF/100 m): 330

### Nominal Velocity of Propagation:

VP (%)  
70

### Nominal Delay:

Delay (ns/ft)  
1.5

### Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)  
28.0

### Maximum Conductor DC Resistance:

DCR @ 20°C (Ohm/100 m)  
9.38

### Max. Operating Voltage - UL:

Voltage  
300 V RMS

### Maximum DCR Unbalanced:

DCR Unbalance @ 20°C (%)  
5

## Electrical Characteristics-Premise (Overall)

### Premise Cable Electricals:

Freq. (MHz)	Max. Attenuation (dB/100 m)	Min. NEXT (dB)	Min. PSNEXT (dB)	Min. SRL (dB)	Fitted Imp. (Ohms)
1	2.56	41.0	No Spec	12.0	100 ± 15%

## 1227A1 Multi-Conductor - Category 3 Nonbonded-Pair Cable

4	5.58	32.0	No Spec	12.0	100 ± 15%
8	8.50	27.0	No Spec	12.0	100 ± 15%
10	9.71	26.0	No Spec	12.0	100 ± 15%
16	13.10	23.0	No Spec	9.96	100 ± 15%

### Notes (Overall)

**Notes:** Jacket sequentially marked at 2 ft. intervals. Third party verified to TIA/EIA-568-B.2, Category 3

### Related Documents:

No related documents are available for this product

### Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
1227A1 Q5HU1000	1,000 FT	14.000 LB	WHITE, NEUTRAL		CAT3 2PR U/UTP CMR BOX
1227A1 008U1000	1,000 FT	14.000 LB	GRAY		CAT3 2PR U/UTP CMR BOX

Revision Number: 2    Revision Date: 04-23-2009

© 2012 Belden, Inc  
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.