



**Product:** [1245A2](#)

CAT3 Horizontal, 4pr, UTP, LS-PVC Jkt, CMP

### Product Description

CAT3, 4-Pair, U/UTP-unshielded, Plenum-CMP, Premise Horizontal cable, 24 AWG solid bare copper conductors, LS-PVC insulation, LS-PVC jacket

### Technical Specifications

#### Product Overview

Suitable Applications:	802.3 10BaseT, 100BaseT4
------------------------	--------------------------

#### Physical Characteristics (Overall)

##### Conductor

AWG	Stranding	Material	No. of Pairs
24	Solid	BC - Bare Copper	4

Conductor Count:	8
Total Number of Pairs:	4

##### Insulation

Material	
PVC - Polyvinyl Chloride	
Bonded-Pair:	N/A

##### Color Chart

Number	Color
1	White/Blue Stripe & Blue
2	White/Orange Stripe & Orange
3	White/Green Stripe & Green
4	White/Brown Stripe & Brown

##### Outer Jacket

Material	Material Trade Name	Nominal Diameter	Ripcord
PVC - Polyvinyl Chloride	Flamarrest®	0.157 in	No

#### Electrical Characteristics

##### Conductor DCR

Max. Conductor DCR	Max. DCR Unbalance
93.8 Ohm/km	5 %

##### Capacitance

Max. Capacitance Unbalance	Nom. Mutual Capacitance
330 pF/100m	19 pF/ft

##### Delay

Frequency [MHz]	Max. Delay	Max. Delay Skew	Nominal Delay	Nominal Velocity of Propagation (VP) [%]
100 MHz	537.6 ns/100m	45 ns/100m	1.5 ns/ft	61%

##### High Frequency

Frequency [MHz]	Max. Insertion Loss (Attenuation)	Min. NEXT [dB]	Min. SRL (Structural Return Loss)	Max./Min. Fitted Impedance
1 MHz	2.6 dB/100m	41.0 dB	12.0 dB	100 ± 15 Ohm
4 MHz	5.6 dB/100m	32.0 dB	12.0 dB	100 ± 15 Ohm
8 MHz	8.5 dB/100m	27.0 dB	12.0 dB	100 ± 15 Ohm
10 MHz	9.7 dB/100m	26.0 dB	12.0 dB	100 ± 15 Ohm
16 MHz	13.1 dB/100m	23.0 dB	10.0 dB	100 ± 15 Ohm

#### Voltage

UL Voltage Rating
300 V RMS

#### Temperature Range

Installation Temperature Range:	0°C To +50°C
UL Temp Rating:	60°C
Storage Temperature Range:	-20°C To +60°C
Operating Temperature Range:	-20°C To +60°C

#### Mechanical Characteristics

Bulk Cable Weight:	18 lbs/1000ft
Max. Pull Tension:	25 lbs
Min. Bend Radius During Installation:	4.75 in
Min. Bend Radius/Minor Axis:	2.25 in

#### Standards

NEC/(UL) Compliance:	CMP
CEC/C(UL) Compliance:	CMP
Data Category:	Category 3
ANSI Compliance:	S-90-661-2012 Category 3, ANSI/NEMA WC-63.1 Category 3
TIA/EIA Compliance:	ANSI/TIA-568-C.2 Category 3
Third Party Performance Verification:	Category 3

#### Applicable Environmental and Other Programs

Environmental Space:	Plenum
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (RoHS 2):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU (RoHS 2 amendment):	Yes
EU Directive Compliance:	Yes
EU CE Mark:	Yes
EU REACH SVHC Compliance (yyyy-mm-dd):	2017-07-10
MII Order #39 (China RoHS):	Yes

#### Suitability

Suitability - Aerial:	No
Suitability - Burial:	No
Suitability - Hazardous Locations:	No
Suitability - Indoor:	Yes
Suitability - Non-Halogenated:	No
Suitability - Oil Resistance:	No
Suitability - Outdoor:	No
Suitability - Sunlight Resistance:	No

#### Flammability, LSOH, Toxicity Testing

UL Flammability:	NFPA 262 Plenum (UL 910)
UL voltage rating:	300 V RMS

## Plenum/Non-Plenum

Plenum (Y/N):	Yes
---------------	-----

## Related Part Numbers

Non-Plenum Number:	1229A1
--------------------	--------

## Variants

Item #	Color	Put-Up Type	Length	UPC
1245A2 009U1000	White	UnReel	1,000 ft	612825109761

## Product Notes

Notes:	Electrical values are expected performance based on cable testing and representative performance within a typical Belden system. Print Includes Descending Footage Markings.
--------	--

## History

Update and Revision:	Revision Number: 0.437 Revision Date: 02-03-2025
----------------------	--

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.