



Product: [8261](#)

Analog Video, RG11, #18 Str TC, 95% BC Braid, PVC Jacket, CXC

### Product Description

18 AWG stranded (7x26) .048" tinned copper conductor, polyethylene insulation, bare copper braid shield (95% coverage), PVC jacket.

### Technical Specifications

#### Product Overview

Suitable Applications:	SDI coax
------------------------	----------

#### Construction Details

RG Type:	11
----------	----

#### Conductor

No. of Elements	Size	Stranding	Nom. Diameter	Material
1	18 AWG	7x26	0.048 in	TC - Tinned Copper

#### Insulation

Material	Nom. Insulation Diameter	Color Code
PE - Polyethylene	0.285 in (7.24 mm)	White

#### Outer Shield

Outer Shield Type	Material	Coverage
Braid	Bare Copper (BC)	95%

#### Outer Jacket

Material	Nom. Diameter
PVC - Polyvinyl Chloride (Non-Contaminating)	0.405 in (10.3 mm)

Overall Cable Diameter (Nominal):	0.405 in (10.3 mm)
-----------------------------------	--------------------

#### Electrical Characteristics

#### Attenuation

Frequency	Nom. Attenuation
1 MHz	0.2 dB/100ft
10 MHz	0.7 dB/100ft
50 MHz	1.3 dB/100ft
100 MHz	2 dB/100ft
200 MHz	2.9 dB/100ft
400 MHz	4.2 dB/100ft
700 MHz	5.8 dB/100ft
900 MHz	6.8 dB/100ft
1000 MHz	7.1 dB/100ft

#### Electricals

Nom. Conductor DCR	Nom. Outer Shield DCR	Nom. Capacitance Cond-to-Shield	Nom. Characteristic Impedance	Nom. Velocity of Prop.
6.1 Ohm/1000ft (20 Ohm/km)	1.2 Ohm/1000ft (3.9 Ohm/km)	20.5 pF/ft (67.3 pF/m)	75 Ohm	66%

## Voltage

UL Voltage Rating
3700 V RMS

## Mechanical Characteristics

### Temperature

UL Temperature	Operating
60°C	-40°C To +60°C

### Bend Radius

Stationary Min.	Installation Min.
4.00 in (102 mm)	4.00 in (102 mm)

Max. Pull Tension:	143 lbs (64.9 kg)
Bulk Cable Weight:	95 lbs/1000ft

## Standards and Compliance

Environmental Suitability:	Indoor/Outdoor, Indoor, Outdoor
Flammability / Reaction to Fire:	[delete], IEC 60332-1-2
CPR Compliance:	CPR Euroclass: Eca
CEC / C(UL) Compliance:	CXC
European Directive Compliance:	EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
UK Regulation Compliance:	UKCA Mark
APAC Compliance:	China RoHS II (GB/T 26572-2011)

## History

Update and Revision:	Revision Number: 0.407 Revision Date: 04-29-2024
----------------------	--

## Part Numbers

### Variants

Item #	Color	Putup Type	Length	UPC	Footnote
8261 010500	Black	Reel	500 ft	612825197447	C
8261 0101000	Black	Reel	1,000 ft	612825358121	C

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.