

## 8448 Multi-Conductor - Antenna Rotor Cable

For more Information  
please call

1-800-Belden1



### Description:

6 - 22 AWG stranded (7x30) and 2 - 18 AWG stranded (16x30) tinned copper conductors, conductors cabled, PVC insulation, PVC jacket.

### Physical Characteristics (Overall)

#### Conductor

##### AWG:

# Conductors	AWG	Stranding	Conductor Material
2	18	16x30	TC - Tinned Copper
6	22	7x30	TC - Tinned Copper

#### Insulation

##### Insulation Material:

Insulation Material	Wall Thickness (in.)	AWG
PVC - Polyvinyl Chloride	.019	18
PVC - Polyvinyl Chloride	.010	22

#### Outer Shield

##### Outer Shield Material:

Outer Shield Material
Unshielded

#### Outer Jacket

##### Outer Jacket Material:

Outer Jacket Material	Nom. Wall Thickness (in.)
PVC - Polyvinyl Chloride	.032

#### Overall Cable

##### Overall Cabling Color Code Chart:

Number	Color
1	Black (18 AWG)
2	White (18 AWG)
3	Red (22 AWG)
4	Green (22 AWG)
5	Brown (22 AWG)
6	Blue (22 AWG)
7	Yellow (22 AWG)
8	Orange (22 AWG)

**Overall Nominal Diameter:** 0.259 in.

### Mechanical Characteristics (Overall)

<b>Operating Temperature Range:</b>	-20°C To +80°C
<b>UL Temperature Rating:</b>	80°C (UL AWM Style 2576)
<b>Bulk Cable Weight:</b>	45.200 lbs/1000 ft.
<b>Max. Recommended Pulling Tension:</b>	86 lbs.
<b>Min. Bend Radius (Install)/Minor Axis:</b>	2.600 in.

## Applicable Specifications and Agency Compliance (Overall)

### Applicable Standards & Environmental Programs

NEC/(UL) Specification:	CMG
CEC/C(UL) Specification:	CMG
AWM Specification:	UL Style 2576 (150 V 80°C)
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	04/01/2005
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

### Flame Test

UL Flame Test:	UL1685 FT4 Loading
C(UL) Flame Test:	FT4

### Suitability

Sunlight Resistance:	Yes
----------------------	-----

## Electrical Characteristics (Overall)

### Nom. Conductor DC Resistance:

Description	DCR @ 20°C (Ohm/1000 ft)
22 AWG	15.6
18 AWG	6.8

### Max. Operating Voltage - UL:

Voltage	Description
300 V RMS	CMG
150 V RMS	UL AWM Style 2576

### Max. Recommended Current:

Current
2.4 Amps per conductor @ 25°C (22 AWG)
4 Amps per conductor @ 25°C (18 AWG)

## Related Documents:

No related documents are available for this product

## Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
8448 060U1000	1,000 FT	49.000 LB	CHROME		2#18,6#22 PVC PVC
8448 060U500	500 FT	25.000 LB	CHROME		2#18,6#22 PVC PVC
8448 0601000	1,000 FT	50.000 LB	CHROME	C	2#18,6#22 PVC PVC
8448 060500	500 FT	25.500 LB	CHROME	C	2#18,6#22 PVC PVC

### Notes:

C = CRATE REEL PUT-UP.

Revision Number: 2    Revision Date: 09-18-2008

© 2012 Belden, Inc  
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications

## 8448 Multi-Conductor - Antenna Rotor Cable

described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.