


Product: [5501UE](#)

Security & Sound, 3 Conductor 22 AWG BC, Riser



Product Description

Security & Commercial Audio Cable, 3 Conductor 22 AWG stranded (7x30) bare copper conductors with polyolefin insulation, Riser, PVC jacket with ripcord.

Technical Specifications

Product Overview

| | |
|------------------------|---|
| Suitable Applications: | Security Systems, Intercom/PA Systems, Sound/Audio Systems, Power Limited Controls, Single Line Telephone |
|------------------------|---|

Physical Characteristics (Overall)

Conductor

| AWG | Stranding | Material | No. of Conductors |
|-----|-----------|------------------|-------------------|
| 22 | 7x30 | BC - Bare Copper | 3 |

| | |
|------------------|---|
| Conductor Count: | 3 |
|------------------|---|

Insulation

| Material | Nominal Wall Thickness |
|--------------------|------------------------|
| PP - Polypropylene | 0.008 in |

Color Chart

| Number | Color |
|--------|-------|
| 1 | Black |
| 2 | Red |
| 3 | White |

Outer Shield Material

| Material |
|-----------|
| No Shield |

Outer Jacket Material

| Material | Nominal Diameter | Nominal Wall Thickness | Ripcord |
|--------------------------|------------------|------------------------|---------|
| PVC - Polyvinyl Chloride | 0.13 in | 0.017 in | Yes |

Construction and Dimensions

Cabling

| Twists |
|----------------|
| 5.333 twist/ft |

Electrical Characteristics

Conductor DCR

| Nominal Conductor DCR |
|-----------------------|
| 16.2 Ohm/1000ft |

Capacitance

| Nom. Capacitance Conductor to Conductor |
|---|
|---|

17 pF/ft

Current

Max. Recommended Current [A]

2.8 Amps per Conductor at 25°C

Voltage

UL Voltage Rating

300 V RMS

Temperature Range

| | |
|-----------------------|----------------|
| UL Temp Rating: | 75°C |
| Operating Temp Range: | -20°C To +75°C |

Mechanical Characteristics

| | |
|-----------------------------|---------------|
| Bulk Cable Weight: | 10 lbs/1000ft |
| Max. Pull Tension: | 27.3 lbs |
| Min Bend Radius/Minor Axis: | 1.25 in |

Standards

| | |
|-----------------------|-------------|
| NEC Articles: | Article 800 |
| NEC/(UL) Compliance: | CMR |
| CEC/C(UL) Compliance: | CMG |

Applicable Environmental and Other Programs

| | |
|---------------------------------------|-------------------------------|
| Environmental Space: | Indoor - Riser |
| EU Directive 2000/53/EC (ELV): | Yes |
| EU Directive 2003/96/EC (BFR): | Yes |
| EU Directive 2011/65/EU (ROHS II): | Yes |
| EU Directive 2012/19/EU (WEEE): | Yes |
| EU Directive Compliance: | EU Directive 2003/11/EC (BFR) |
| EU CE Mark: | Yes |
| EU RoHS Compliance Date (yyyy-mm-dd): | 2005-04-01 |
| MII Order #39 (China RoHS): | Yes |

Flammability, LS0H, Toxicity Testing

| | |
|---------------------|-----------------------|
| C(UL) Flammability: | FT4 |
| UL Flammability: | UL1666 Vertical Shaft |
| UL voltage rating: | 300 V RMS |

Plenum/Non-Plenum

| | |
|----------------|--------|
| Plenum (Y/N): | No |
| Plenum Number: | 6501UE |

Part Number

Variants

| Item # | Color | Putup Type | Length | UPC/EAN |
|-----------------|-------|--------------|----------|---------------|
| 5501UE.00U305 | Gray | Reel | 305 m | 8719605008664 |
| 5501UE 0081000 | Gray | Reel | 1,000 ft | 612825163244 |
| 5501UE 008U1000 | Gray | UnReel | 1,000 ft | 612825425878 |
| 5501UE 008Z1000 | Gray | ReelTuff Box | 1,000 ft | 612825163268 |

Footnote: C - CRATE REEL PUT-UP.

History

| | |
|----------------------|--|
| Update and Revision: | Revision Number: 0.270 Revision Date: 06-24-2020 |
|----------------------|--|

© 2020 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.