



Product: [8178](#) 

RS232/422 Low Cap, #24-18pr, FPO, Individ.& O/A Foils+Braid, PVC Jkt, CM, 100Ω

Product Description

Computer EIA RS-232/422, Digital Audio Cable, 24 AWG stranded (7x32) tinned copper conductors, Datalene® insulation, twisted pairs individually Beldfoil® shielded + overall 100% Beldfoil® + tinned copper braid shield (65% coverage), drain wire, PVC jacket.

Technical Specifications

Product Overview

Suitable Applications:	rs-232 extended distance applications; rs-422 applications; computer communications; low voltage analog signals (4-20ma, 0-10v, ...); low voltage digital control (24v, ...); digital audio; panel wiring
------------------------	---

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	No. of Pairs
24	7x32	TC - Tinned Copper	18

Conductor Count:	36
------------------	----

Insulation

Material	Material Trade Name	Nominal Wall Thickness
PE - Polyethylene (Foam)	Datalene®	0.019 in

Color Chart

Number	Color
1	Black & Red
2	Black & White
3	Black & Green
4	Black & Blue
5	Black & Yellow
6	Black & Brown
7	Black & Orange
8	Red & White
9	Red & Green
10	Red & Blue
11	Red & Yellow
12	Red & Brown
13	Red & Orange
14	Green & White
15	Green & Blue
16	Green & Yellow
17	Green & Brown
18	Green & Orange

Inner Shield Material

Type	Material	Material Trade Name	Coverage [%]	Drainwire Material	Drainwire AWG	Drainwire Construction n x D
Tape	Alum / Poly	Beldfoil®	100 %	TC - Tinned Copper	24	Stranded

Outer Shield Material

Type	Layer	Material	Material Trade Name	Coverage [%]
Tape	1	Alum / Poly	Beldfoil®	100 %
Braid	2	TC - Tinned Copper		65 %

Outer Jacket Material

Material	Nominal Diameter	Nominal Wall Thickness
PVC - Polyvinyl Chloride	0.696 in	0.065 in

Electrical Characteristics

Conductor DCR

Individual Pair Nominal Shield DCR	Nominal Conductor DCR	Nominal Outer Shield DCR
18 Ohm/1000ft	24 Ohm/1000ft	2.6 Ohm/1000ft

Capacitance

Nom. Capacitance Conductor to Conductor	Nom. Capacitance Conductor to Other Conductor to Shield
12.5 pF/ft	22 pF/ft

Impedance

Nominal Characteristic Impedance
100 Ohm

Delay

Max. Delay Skew	Nominal Velocity of Propagation (VP) [%]
78 ns/100m	78 %

Current

Max. Recommended Current [A]
1 Amp per conductor @ 25°C A

Voltage

UL Voltage Rating
300 V RMS

Temperature Range

UL Temp Rating:	60°C (UL AWM Style 2493)
Operating Temp Range:	-40°C To +60°C

Mechanical Characteristics

Bulk Cable Weight:	214 lbs/1000ft
Max Recommended Pulling Tension:	364 lbs
Min Bend Radius/Minor Axis:	7 in

Dimensions (WxHxD)

Width	Height
8.5	8.465

Standards

NEC/(UL) Specification:	CM
CEC/C(UL) Specification:	CM

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2004-01-01
MII Order #39 (China RoHS):	Yes

Flammability, LS0H, Toxicity Testing

UL Flammability:	UL1581 Vertical Tray
UL voltage rating:	300 V RMS

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Part Number

Variants

Item #	Color	Putup Type	Length	UPC
8178 060100	Chrome	Reel	100 ft	612825195856
8178 0601000	Chrome	Reel	1,000 ft	612825195863
Footnote:		C - CRATE REEL PUT-UP.		

History

Update and Revision:	Revision Number: 0.258 Revision Date: 04-28-2020
----------------------	--

© 2020 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.