



For more Information
please call

1-800-Belden1



Description:

26 AWG stranded (7x34) .020" silver-plated copper-covered steel conductor, TFE Teflon® insulation, silver-plated copper braid shield (95% coverage), FEP jacket.

Physical Characteristics (Overall)

Conductor

AWG:

# Coax	AWG	Stranding	Conductor Material	Dia. (in.)
1	26	7x34	SPCCS - Silver Plated Copper Covered Steel	.020

Insulation

Insulation Material:

Insulation Trade Name	Insulation Material	Dia. (in.)
Teflon®	TFE - Tetrafluoroethylene	.058

Outer Shield

Outer Shield Material:

Type	Outer Shield Material	Coverage (%)
Braid	SPC - Silver Plated Copper	95

Outer Jacket

Outer Jacket Material:

Outer Jacket Material
FEP - Fluorinated Ethylene Propylene

Overall Cable

Overall Nominal Diameter: 0.098 in.

Mechanical Characteristics (Overall)

Operating Temperature Range: -70°C To +200°C

Non-UL Temperature Rating: 200°C

Bulk Cable Weight: 10 lbs/1000 ft.

Max. Recommended Pulling Tension: 21 lbs.

Min. Bend Radius (Install)/Minor Axis: 1 in.

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

EU CE Mark: No

EU Directive 2000/53/EC (ELV): Yes

EU Directive 2002/95/EC (RoHS): Yes

EU RoHS Compliance Date (mm/dd/yyyy): 04/01/2005

EU Directive 2002/96/EC (WEEE): Yes

EU Directive 2003/11/EC (BFR): Yes

CA Prop 65 (CJ for Wire & Cable): Yes

MII Order #39 (China RoHS): Yes

Military Specification:	MIL-C-17, M17/113-RG316
--------------------------------	-------------------------

RG Type:	316/U
-----------------	-------

Plenum/Non-Plenum

Plenum (Y/N):	No
----------------------	----

Electrical Characteristics (Overall)

Nom. Characteristic Impedance:

Impedance (Ohm)

50

Nom. Inductance:

Inductance (µH/ft)

0.067

Nom. Capacitance Conductor to Shield:

Capacitance (pF/ft)

29.0

Nominal Velocity of Propagation:

VP (%)

69.5

Nominal Delay:

Delay (ns/ft)

1.48

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

84.1

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

6.5

Nom. Attenuation:

Freq. (MHz) Attenuation (dB/100 ft.)

1.000	1.200
10.000	2.700
50.000	5.600
100.000	8.300
200.000	12.000
400.000	17.500
700.000	23.700
900.000	27.300
1000.000	29.000
1500.000	36.500
2000.000	42.500
2400.000	47.200
3000.000	53.600

Max. Operating Voltage - Other:

Voltage	Description
Military Specification	900 V RMS

Minimum Structural Return Loss:

Freq. (MHz) Min. SRL (dB)

50.000	30.000
100.000	30.000
400.000	23.000
1000.000	21.000
3000.000	17.000

Notes (Overall)

Notes: Teflon® is a registered trademark of E. I. duPont de Nemours and Co. used under license by Belden, Inc.

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
84316 001100	100 FT	1.100 LB	BROWN	E	M17/13-RG316 COAX
84316 0011000	1,000 FT	11.000 LB	BROWN	E	M17/13-RG316 COAX
84316 001500	500 FT	6.000 LB	BROWN	E	M17/13-RG316 COAX

Notes:

E = MAY CONTAIN MORE THAN 1 PIECE. MINIMUM LENGTH OF ANY ONE PIECE IS 25'

Revision Number: 5 Revision Date: 03-28-2012

© 2012 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.