


1668A Multi-Conductor - Category 5 Nonbonded-Pair ScTP Cable



For more Information
please call

1-800-Belden1



Description:

24 AWG solid bare copper conductors, non-plenum, dual, Polyolefin insulation, twisted pairs, overall Beldfoil® shield, drain wire, rip cord, see color code chart (below), Gray PVC jacket with polarity rib.

Usage (Overall)

Suitable Applications: Premise Horizontal Cable

Physical Characteristics (Overall)

Conductor

AWG:

# Pairs	AWG	Stranding	Conductor Material
8	24	Solid	BC - Bare Copper

Insulation

Insulation Material:

Insulation Material
PO - Polyolefin

Outer Shield

Outer Shield Material:

Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
Beldfoil®	Tape	Aluminum Foil-Polyester Tape	100

Outer Shield Drain Wire AWG:

AWG	Stranding	Drain Wire	Conductor Material
24	Solid	TC - Tinned Copper	

Outer Jacket

Outer Jacket Material:

Outer Jacket Material
PVC - Polyvinyl Chloride

Outer Jacket Ripcord: Yes

Overall Cable

Overall Nominal Diameter: 0.518 x 0.254 in.

Pair

Pair Color Code Chart:

Number	Color
1	White/Blue Stripe & Blue
2	White/Orange Stripe & Orange
3	White/Green Stripe & Green
4	White/Brown Stripe & Brown

Mechanical Characteristics (Overall)

Operating Temperature Range: -20°C To +75°C

Bulk Cable Weight: 60 lbs/1000 ft.

Max. Recommended Pulling Tension: 50 lbs.

Min. Bend Radius (Install)/Minor Axis: 2.400 in.

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification:	CM, UL444
CEC/C(UL) Specification:	CM
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	01/01/2004
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes
Telecommunications Standards:	568 TSB 36, Category 5
Other Specification:	Each Leg ETL verified to TSB 36 Category 5

Flame Test

UL Flame Test:	UL1685 UL Loading
CSA Flame Test:	FT1

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Electrical Characteristics (Overall)

Nom. Mutual Capacitance:

Capacitance (pF/ft)	15
---------------------	----

Maximum Capacitance Unbalance (pF/100 m):	330
---	-----

Nominal Velocity of Propagation:

VP (%)	67
--------	----

Maximum Delay:

Delay (ns/100 m)	538 @ 100MHz
------------------	--------------

Max. Delay Skew:

Delay Skew (ns/100 m)	45
-----------------------	----

Maximum Conductor DC Resistance:

DCR @ 20°C (Ohm/100 m)	9.38
------------------------	------

Max. Operating Voltage - UL:

Voltage	300 V RMS
---------	-----------

Maximum DCR Unbalanced:

DCR Unbalance @ 20°C (%)	5
--------------------------	---

Electrical Characteristics-Premise (Overall)

Premise Cable Electricals:

Freq. (MHz)	Max. Attenuation (dB/100 m)	Min. NEXT (dB)	Min. PSNEXT (dB)	Min. SRL (dB)	Fitted Imp. (Ohms)
1	2.0	62.3	No Spec	No Spec	100 ± 15%

1668A Multi-Conductor - Category 5 Nonbonded-Pair ScTP Cable

4	4.1	53.3	No Spec	No Spec	100 ± 15%
8	5.8	48.8	No Spec	No Spec	100 ± 15%
10	6.5	47.3	No Spec	No Spec	100 ± 15%
16	8.2	44.3	No Spec	No Spec	100 ± 15%
20	9.3	42.8	No Spec	No Spec	100 ± 15%
25	10.4	41.3	No Spec	No Spec	100 ± 15%
31.25	11.7	39.9	No Spec	No Spec	100 ± 15%
62.5	17.0	35.4	No Spec	No Spec	100 ± 15%
100	22.0	32.3	No Spec	No Spec	100 ± 15%

Notes (Overall)

Notes: Leg One = 4pr Cat 5, Leg Two = 4pr Cat 5, Color code and shielding applies to both legs, A polarity rib is applied to one leg. Not Compatible with RJ11/12/45 Connectors. Jacket sequentially marked at 2 ft. intervals. Third party verified to TIA/EIA-568-TSB 36, Category 5 (Leg 1 & 2).

Related Documents:

No related documents are available for this product

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
1668A F6H1000	1,000 FT	70.000 LB	GRAY, DARK PEARL	C Z	CAT5 2X4PR F/UTP CM REEL
1668A F6H1640	1,640 FT	108.240 LB	GRAY, DARK PEARL	C N	CAT5 2X4PR F/UTP CM REEL

Notes:

C = CRATE REEL PUT-UP.

N = FINAL PUT-UP LENGTH MAY VARY -0% TO +10% FROM LENGTH SHOWN.

Z = FINAL PUT-UP LENGTH MAY VARY (+ OR -) 10% FOR SPOOLS OR REELS AND (+ OR -) 5% FOR UNREEL CARTONS FROM LENGTH SHOWN.

Revision Number: 1 Revision Date: 04-23-2009

© 2012 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.