

8732 Multi-Conductor - Audio, Control and Instrumentation Cable



For more Information
please call

1-800-Belden1



Description:

Combination, 22 AWG stranded (7x30) TC conductors, polyethylene insulation, conductors cabled, TC braid shield over one pair (62% coverage), PVC jacket.

Physical Characteristics (Overall)

Conductor

AWG:

# Pairs	AWG	Stranding	Conductor Material
2	22	7x30	TC - Tinned Copper

Insulation

Insulation Material:

Insulation Material	Wall Thickness (in.)
PE - Polyethylene	.020

Inner Shield

Inner Shield Material:

Layer #	Type	Inner Shield Material	Coverage (%)
1st Pair	Braid	TC - Tinned Copper	62
2nd Pair	Unshielded		

Outer Shield

Outer Shield Material:

Outer Shield Material
Unshielded

Outer Jacket

Outer Jacket Material:

Outer Jacket Material	Nom. Wall Thickness (in.)
PVC - Polyvinyl Chloride	.030

Overall Cable

Overall Nominal Diameter: 0.206 x 332.000 in.

Pair

Pair Color Code Chart:

Number	Color
1	Black, Clear
2	Black, Clear

Pair Lay Length & Direction:

Lay Length (in.)
1.500

Mechanical Characteristics (Overall)

Operating Temperature Range:	-20°C To +60°C
UL Temperature Rating:	60°C (UL AWM Style 2094)
Bulk Cable Weight:	34.900 lbs/1000 ft.
Max. Recommended Pulling Tension:	59 lbs.
Min. Bend Radius (Install)/Minor Axis:	2 in.

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification:	CM
CEC/C(UL) Specification:	CM
AWM Specification:	UL Style 2094 (300 V 60°C)
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	01/01/2004
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Flame Test

UL Flame Test:	UL1685 UL Loading
----------------	-------------------

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Electrical Characteristics (Overall)

Nom. Characteristic Impedance:

Description	Impedance (Ohm)
Shielded pair	74

Nom. Capacitance Conductor to Shield:

Capacitance (pF/ft)
37 (shielded pair only)

Nom. Capacitance Cond. to Other Conductor & Shield:

Capacitance (pF/ft)
21

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)
15.4

Maximum Conductor DC Resistance:

DCR @ 20°C (Ohm/100 m)
10.8

Max. Operating Voltage - UL:

Voltage
300 V RMS (UL AWM Style 2094)

Max. Recommended Current:

Current
2.3 Amps per conductor @ 25°C

Related Documents:

No related documents are available for this product

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
8732 0601000	1,000 FT	40.000 LB	CHROME	C	1#22 SH PR,2#22 FRPE PVC

Notes:

C = CRATE REEL PUT-UP.

8732 Multi-Conductor - Audio, Control and Instrumentation Cable

Revision Number: 1 Revision Date: 09-18-2008

© 2012 Belden, Inc.
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.