



Part Number: 83030

Lead Wire, #16 Str SPC, TFE Ins, AWM 1180 300V 200C TYPE EE

[Request Sample](#)

Product Description

High Temp Plastic Lead Wire, 16AWG (19x29) Silver Plated Copper, TFE Insulation, AWM 1180 300V 200C TYPE EE MIL-W-16878/5 1000V 200C

Technical Specifications

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	No. of Conductors
16	19x29	SCC - Silver-coated Copper	1

Conductor Count: 1

Insulation

Material	Nominal Diameter	Nominal Wall Thickness
TFE - Tetrafluoroethylene	0.0875 in	0.016 in

Outer Jacket Material

Material	Nominal Diameter
No Jacket	0.088 in

Electrical Characteristics

Conductor DCR

Nominal Conductor DCR
4 Ohm/1000ft

Current

Element	Max. Recommended Current [A]
Mil-Std-975M Table 3.16 (single wire)	Mil-Std-975M Table 3.16 (single wire): 13 amps

Voltage

Description	UL Description	UL Voltage Rating	Voltage Rating [V]
Mil-W-16878/5	UL AWM 1180	300 V RMS UL AWM 1180	1000V RMS Mil-W-16878/5

Temperature Range

UL Temp Rating:	200°C
Operating Temp Range:	-70°C To +200°C

Mechanical Characteristics

Bulk Cable Weight:	11 lbs/1000ft
--------------------	---------------

Standards

UL AWM Style:	1180
Military Specification:	NEMA HP3, MIL-W-16878/5 (Except For Stranding)

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2005-04-01
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Flammability, LSOH, Toxicity Testing

UL Flammability:	VW-1
UL voltage rating:	300 V RMS (UL AWM Style 1180)

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Part Number

Variants

Item #	Color	UPC	Length	Footnote
83030 010100	Black	612825354598	100 ft	
83030 0101000	Black	612825399629	1,000 ft	S W
83030 010500	Black	612825353690	500 ft	S W
83030 006100	Blue, Light	612825354628	100 ft	
83030 0061000	Blue, Light	612825399605	1,000 ft	S W
83030 001100	Brown	612825354581	100 ft	
83030 0011000	Brown			S W
83030 008100	Gray	612825354536	100 ft	
83030 0081000	Gray		1,000 ft	S W
83030 005100	Green, Dark	612825354611	100 ft	
83030 0051000	Green, Dark		1,000 ft	S W
83030 0031000	Orange	612825399582	1,000 ft	S W
83030 003100	Orange			
83030 002100	Red	612825354604	100 ft	
83030 0021000	Red	612825399575	1,000 ft	S W
83030 007100	Violet		100 ft	
83030 0071000	Violet		1,000 ft	S W
83030 009100	White	612825354574	100 ft	
83030 0091000	White	612825399612	1,000 ft	S W
83030 009500	White		500 ft	S W
83030 0041000	Yellow	612825399599	1,000 ft	S W
83030 004100	Yellow			

Footnote:	S - STRIPING ADDERS FOR TYPES E AND EE: 1, 2, 3 STRIPES. MINIMUM ORDER 10,000' PER STRIPE COMBINATION. (SEE STRIPING ADDER TABLE)
Footnote:	W - MAY CONTAIN MORE THAN 1 PIECE. MINIMUM LENGTH OF ANY ONE PIECE IS 75'.

History

Update and Revision:	Revision Number: 0.276 Revision Date: 08-22-2019
----------------------	--

© 2019 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.