



Part Number: 8446

Electronic, 4+2 C #18+22 Str TC, PVC Ins, PVC Jkt, CMG

[Request Sample](#)

Product Description

Electronic, 4+2 Conductor 18+22AWG (16x30+7x30) Tinned Copper, PVC Insulation, PVC Outer Jacket, CMG

Technical Specifications

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	No. of Conductors
22	7x30	TC - Tinned Copper	6
18	19x30	TC - Tinned Copper	2

Conductor Count:	6
Conductor Size:	22 AWG

Insulation

Element	Material	Nominal Wall Thickness
22	PVC - Polyvinyl Chloride	0.011 in
18	PVC - Polyvinyl Chloride	0.019 in

Color Chart

Number	Color
22	Red
22	Green
22	Brown
22	Blue
18	White
18	Black

Outer Shield Material

Material
Unshielded

Outer Jacket Material

Material	Nominal Diameter	Nominal Wall Thickness
PVC - Polyvinyl Chloride	0.236 in	0.032 in

Electrical Characteristics

Conductor DCR

Element	Nominal Conductor DCR
22 AWG	15.5 Ohm/1000ft
18 AWG	6.8 Ohm/1000ft

Capacitance

Nom. Capacitance Conductor to Conductor	Nom. Capacitance Conductor to Other Conductor to Ground	Nom. Capacitance Conductor to Other Conductor to Shield
30 pF/ft	54 pF/ft	54 pF/ft

Current

Element	Max. Recommended Current [A]
22 AWG	2.5 Amps per conductor @ 25°C
18 AWG	5.6 Amps per conductor @ 25°C

Voltage

UL Description	UL Voltage Rating
UL AWM Style 2576	150 V RMS
CMG	300 V RMS

Temperature Range

UL Temp Rating:	80°C (UL AWM Style 2576)
Operating Temp Range:	-20°C To +80°C

Mechanical Characteristics

Bulk Cable Weight:	39 lbs/1000ft
Max Recommended Pulling Tension:	78 lbs
Min Bend Radius/Minor Axis:	2.5 in

Standards

NEC Articles:	800
NEC/(UL) Specification:	CMG
CEC/C(UL) Specification:	CMG
UL AWM Style:	UL Style 2576 (150 V 80°C)
CPR Euroclass:	Eca

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2005-04-01
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Flammability, LS0H, Toxicity Testing

UL Flammability:	UL1685 FT4 Loading
CSA Flammability:	FT4
ISO/IEC Flammability:	IEC 60332-1-2
UL voltage rating:	150 V RMS

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Part Number

Variants

Item #	Color	UPC	Length	Footnote
8446 060100	Chrome	612825207542	100 ft	
8446 0601000	Chrome	612825207559	1,000 ft	C
8446 060500	Chrome	612825207566	500 ft	C
8446 060U1000	Chrome	612825207528	1,000 ft	
8446 060U500	Chrome	612825207535	500 ft	

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

© 2019 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.