



Product: [9503](#)

RS-232, #24-3pr, SR-PVC, O/A Foil, PVC Jkt, CMG, 75Ω

Product Description

Computer EIA RS-232 Cable, 24 AWG stranded (7x32) tinned copper conductors, semi-rigid PVC insulation, twisted pairs, overall Beldfoil® shield (100% coverage), 24 AWG stranded tinned copper drain wire, PVC jacket.

Technical Specifications

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	No. of Conductors	No. of Pairs
24	7x32	TC - Tinned Copper	6	3

Conductor Count:	6
------------------	---

Insulation

Material	Nominal Wall Thickness
S-R PVC - Semi-Rigid Polyvinyl Chloride	0.011 in

Color Chart

Number	Color
1	Black & Red
2	Black & White
3	Black & Green

Outer Shield Material

Type	Material	Material Trade Name	Coverage [%]	Drainwire Material	Drainwire AWG	Drainwire Construction n x D
Tape	Aluminum/Polyester	Beldfoil®	100 %	TC - Tinned Copper	24	7x32 mm

Outer Jacket Material

Material	Nominal Diameter	Nominal Wall Thickness
PVC - Polyvinyl Chloride	0.232 in	0.032 in

Electrical Characteristics

Conductor DCR

Nominal Conductor DCR	Nominal Outer Shield DCR
24 Ohm/1000ft	17 Ohm/1000ft

Capacitance

Nom. Capacitance Conductor to Conductor	Nom. Capacitance Conductor to Other Conductor to Shield
30 pF/ft	50 pF/ft

Impedance

Nominal Characteristic Impedance
75 Ohm

Delay

Max. Delay Skew	Nominal Velocity of Propagation (VP) [%]

60 ns/100m	60 %
------------	------

Current

Max. Recommended Current [A]

1.76 Amps per conductor @ 25°C A

Voltage

UL Voltage Rating

300 V RMS

Temperature Range

UL Temp Rating:	80°C (UL AWM Style 2464)
Operating Temp Range:	-30°C To +80°C

Mechanical Characteristics

Bulk Cable Weight:	26 lbs/1000ft
Max Recommended Pulling Tension:	33 lbs
Min Bend Radius/Minor Axis:	2.5 in

Standards

NEC/(UL) Specification:	CMG
CEC/C(UL) Specification:	CMG
UL AWM Style:	2464 (300 V 80°C)
CSA AWM Specification:	AWM I A
CPR Euroclass:	Eca

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2005-04-01
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Flammability, LSOH, Toxicity Testing

UL Flammability:	UL1685 FT4 Loading
CSA Flammability:	FT4
ISO/IEC Flammability:	IEC 60332-1-2
UL voltage rating:	300 V RMS

Plenum/Non-Plenum

Plenum (Y/N):	No
Plenum Number:	89503, 82503

Part Number

Variants

Item #	Color	UPC	Length	Footnote
9503.0030	Chrome		30 m	
9503.00U152	Chrome		152 m	
9503.00U305	Chrome		305 m	
9503.01152	Chrome		152 m	
9503.01305	Chrome		305 m	
9503 060100	Chrome	612825254201	100 ft	
9503 0601000	Chrome	612825254218	1,000 ft	C
9503 060500	Chrome	612825254225	500 ft	C
9503 0605000	Chrome	612825254232	5,000 ft	C

9503 060U1000	Chrome	612825254188	1,000 ft	
9503 060U500	Chrome	612825254195	500 ft	
9503.K030	Chrome		30 m	
9503.K1305	Chrome		305 m	

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

History

Update and Revision:	Revision Number: 0.299 Revision Date: 08-22-2019
----------------------	--------------------------------------------------

© 2020 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.