

## Vinyl Cloth Adhesive Wire & Cable Labels (B-498)

Printer automatically repeats your text to fill the label for maximum readability.

- **B-498 Repositionable Vinyl Cloth** - material's special adhesive stays put, but marker can be removed and reapplied if necessary. Temp Range -40°F to 175°F (-40°C to 70°C). UL Recognized.




Figure 29



Fits Printer Models	Diagram	Catalog #	B#	Material	Color	Approx. Wire Gauge*	Max. Wire Dia. Inch (mm)	Label Width A Inch (mm)	Label Height B Inch (mm)	Labels/ Roll	Ribbon in Cartridge
BMP41, 51, 53	Fig. 29	M-7-498	B-498	Vinyl	BK on WT	22 - 16 Gauge	0.110 (2.8)	0.500 (12.7)	0.500 (12.7)	240	R6200
BMP41, 51, 53	Fig. 29	M-11-498	B-498	Vinyl	BK on WT	16 - 10 Gauge	0.160 (4.1)	0.750 (19.1)	0.500 (12.7)	220	R6200
BMP41, 51, 53	Fig. 29	M-48-498	B-498	Vinyl	BK on WT	12 - 10 Gauge	0.210 (5.3)	1.000 (25.4)	0.750 (19.1)	180	R6200
BMP41, 51, 53	Fig. 29	M-49-498	B-498	Vinyl	BK on WT	12 - 10 Gauge	0.210 (5.3)	1.000 (25.4)	1.000 (25.4)	160	R6200
BMP41, 51, 53	Fig. 29	M-131-498	B-498	Vinyl	BK on WT	10 - 4 Gauge	0.270 (6.7)	1.000 (25.4)	0.500 (12.7)	180	R6200
BMP41, 51, 53	Fig. 29	M-91-498	B-498	Vinyl	BK on WT	10 - 4 Gauge	0.270 (6.7)	1.500 (38.1)	1.000 (25.4)	120	R6200

## Patch Panel, Punch Block, Desi Strip and Faceplate Labels (B-412, and B-422)

Create a fully-formatted serialized punch block label to fit your equipment or label your ports, jacks and outlets with adhesive labels or slide-in strips.

- **B-412 Polypropylene Tags** - Non-Adhesive Slide-in Strips
- **B-422 Polyester Material** - Permanent adhesive, good for powder-coated/textured surfaces. Temp. Range: -40°F to 212°F (-40°C to 100°C). UL recognized.




Figure 29




Figure 33c



Fits Printer Models	Diagram	Catalog #	B#	Material	Color	Label Width A Inch (mm)	Roll Length B Inch (mm)	Labels/Roll	Ribbon in Cartridge
<b>B-412 Polypropylene Tags</b>									
BMP41, 51, 53	Fig. 33c	MC-375-412	B-412	Polypropylene	BK on WT	0.375 (9.5)	20 ft (6.1 m)	1 roll (cont.)	R4300
BMP41, 51, 53	Fig. 33c	MC-475-412	B-412	Polypropylene	BK on WT	0.475 (12.1)	20 ft (6.1 m)	1 roll (cont.)	R4300
BMP41, 51, 53	Fig. 33c	MC-625-412	B-412	Polypropylene	BK on WT	0.625 (15.8)	20 ft (6.1 m)	1 roll (cont.)	R4300
<b>B-422 Polyester Material</b>									
BMP41, 51, 53	Fig. 33c	MC-375-422	B-422	Polyester	BK on WT	0.375 (9.5)	25 ft (7.6 m)	1 roll (cont.)	R6000
BMP41, 51, 53	Fig. 33c	MC-475-422	B-422	Polyester	BK on WT	0.475 (12.1)	25 ft (7.6 m)	1 roll (cont.)	R6000
BMP41, 51, 53	Fig. 29	M-7-422	B-422	Polyester	BK on WT	0.500 (12.7)	0.500 (12.7)	280	R6000
BMP41, 51, 53	Fig. 29	M-89-422	B-422	Polyester	BK on WT	0.500 (12.7)	1.500 (38.1)	180	R6000
BMP41, 51, 53	Fig. 29	M-90-422	B-422	Polyester	BK on WT	0.750 (19.1)	1.500 (38.1)	180	R6000
BMP41, 51, 53	Fig. 29	M-47-422	B-422	Polyester	BK on WT	1.000 (25.4)	0.500 (12.7)	480	R6000

## Terminal Block Adhesive Strips (B-498)

When using terminal block mode, printer can serialize and pre-space to your special thin widths to fit terminal blocks.

- **B-498 Repositionable Vinyl Cloth Material** - Special adhesive stays put, but marker can be removed and reapplied if necessary. Temp Range -40°F to 175°F (-40°C to 70°C). UL Recognized.





Figure 33c



Fits Printer Models	Diagram	Catalog #	B#	Material	Color	Label Width A Inch (mm)	Roll Length B Inch (mm)	Labels/Roll	Ribbon in Cartridge
BMP41, 51, 53	Fig. 33c	MC-240-498	B-498	Vinyl	BK on WT	0.240 (6.1)	16 ft (4.9 m)	1 roll (cont.)	R6200
BMP41, 51, 53	Fig. 33c	MC-318-498	B-498	Vinyl	BK on WT	0.318 (8.1)	16 ft (4.9 m)	1 roll (cont.)	R6200
BMP41, 51, 53	Fig. 33c	MC-375-498	B-498	Vinyl	BK on WT	0.375 (9.5)	20 ft (6.1 m)	1 roll (cont.)	R6200