



Product: [1673J](#)

50 Ohm Microwave, RG402, #19 SPCCS, PVC Jacket



## Product Description

RG-402/U type, 19 AWG solid .036" silver-plated copper-covered steel conductor, TFE Teflon® Insulation, copper-tin composite shield (100% coverage), PVC jacket.

## Technical Specifications

### Physical Characteristics (Overall)

#### Conductor

AWG	Stranding	Material	Nominal Diameter	No. of Coax
19	Solid	SCCS - Silvered Copper Covered Steel	0.036 in	1

Conductor Count: 1

#### Insulation

Material	Material Trade Name	Nominal Diameter
PTFE - Polytetrafluoroethylene	Teflon®	0.116 in

#### Outer Shield

Type	Layer	Material	Coverage [%]
Tape	1	Bare Copper (BC)	100%
Braid	2	Tinned Copper (TC + Tin Filled)	100%

#### Outer Jacket

Material	Nominal Diameter
PVC - Polyvinyl Chloride	0.178 in

### Electrical Characteristics

#### Conductor DCR

Nominal Conductor DCR	Nominal Conductor DCR	Conductor Resistance	Nominal Outer Shield DCR	Outer Conductor DCR
20.5 Ohm/1000ft	20.5 Ohm/1000ft		4.5 Ohm/1000ft	4.5 Ohm/1000ft

#### Capacitance

Nom. Capacitance Conductor to Shield
29.5 pF/ft

#### Inductance

Nominal Inductance
0.07 µH/ft

#### Impedance

Nominal Characteristic Impedance
50 Ohm

#### High Frequency (Nominal/Typical)

Frequency [MHz]	Nom. Insertion Loss
500 MHz	8 dB/100ft

1000 MHz	12 dB/100ft
2000 MHz	18.1 dB/100ft
3000 MHz	22.9 dB/100ft
5000 MHz	31 dB/100ft
7000 MHz	37.8 dB/100ft
10000 MHz	46.6 dB/100ft
15000 MHz	59.1 dB/100ft
18000 MHz	65.8 dB/100ft
20000 MHz	70 dB/100ft

#### Delay

Nominal Delay	Nominal Velocity of Propagation (VP) [%]
1.46 ns/ft	70%

#### High Frequency

Frequency [MHz]	Max. Insertion Loss (Attenuation)
500 MHz	9.5 dB/100ft
1000 MHz	14.5 dB/100ft
3000 MHz	26.5 dB/100ft
5000 MHz	36 dB/100ft
10000 MHz	54 dB/100ft
20000 MHz	84 dB/100ft

#### Power Rating

Frequency [MHz]	Max. Power Rating [W]	Nominal Power Rating [W]
500 MHz	600 W	600 W
1,000 MHz	401 W	401 W
2,000 MHz	268 W	268 W
3,000 MHz	211 W	211 W
5,000 MHz	157 W	157 W
7,000 MHz	129 W	129 W
10,000 MHz	105 W	105 W
15,000 MHz	83 W	83 W
18,000 MHz	74 W	74 W
20,000 MHz	70 W	70 W

#### Voltage

Non-UL Voltage Rating	UL Voltage Rating
1900 V RMS	30 V RMS

#### VSWR

Element	Frequency [MHz]	Max. VSWR
Ramp Function, End Points	500 MHz	1.1
	20000 MHz	1.3

### Temperature Range

Non-UL Temp Rating:	105°C
UL Temp Rating:	105°C
Operating Temperature Range:	-40°C To +105°C

### Mechanical Characteristics

Bulk Cable Weight:	32 lbs/1000ft
Max. Pull Tension:	70 lbs
Min Bend Radius (Overall):	1.5 in
Min. Bend Radius During Installation:	0.25 in
Min Flexing Radius:	0.75 in

### Standards

UL AWM Style Compliance:	AWM 10245
RG Type:	402

## Applicable Environmental and Other Programs

Environmental Space:	Indoor/Outdoor
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/11/EC (BFR):	Yes
EU Directive 2011/65/EU (RoHS 2):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU (RoHS 2 amendment):	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	No
MII Order #39 (China RoHS):	Yes

## Suitability

Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes

## Flammability, LSOH, Toxicity Testing

UL Flammability:	Horizontal Wire
UL voltage rating:	30 V RMS

## Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

## Related Part Numbers

### Variants

Item #	Color	Put-Up Type	Length	UPC
1673J 010100	Black	Reel	100 ft	612825120452
1673J 010500	Black	Reel	500 ft	612825120469

Footnote:	C - CRATE REEL PUT-UP., V - 250' PUT-UP EXACT LENGTH MAXIMUM OF 3 PIECES, MINIMUM LENGTH 50'. 500' PUT-UP EXACT LENGTH MAXIMUM OF 5 PIECES, MINIMUM LENGTH 50'. 1000' PUT-UP EXACT LENGTH MAXIMUM OF 8 PIECES, MINIMUM LENGTH 50'.
-----------	--

## Product Notes

Notes:	Teflon® is a registered trademark of E. I. duPont de Nemours and Co. used under license by Belden, Inc.
--------	---

## History

Update and Revision:	Revision Number: 0.402 Revision Date: 04-29-2024
----------------------	--

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.