


RF240A2JEGA Datasheet

Product Name // 2.4mm Jack Straight 2 Hole Flange RF Connector

 [View Product Page](#)



// Product Description:

- 2.4mm Jack Straight 2 Hole Flange RF Connector
 - Maximum Voltage: 150V
 - Temperature range: -40°C to +85°C
 - Frecuency range: 0GHz - 50GHz
 - VSWR: <1.30
- Dielectric withstanding Voltage: >500V
 - Impedance: 50Ohm
 - Body Material: Stainless Steel Passivation
 - Contact Material: Beryllium Copper

// General Information:

Product Display Title:	2.40mm Series Socket 2 Hole Flange
Product Family:	Radio Frequency Connectors
Product Series:	2.40mm Series
Body Length:	10.80mm
Body Material:	Stainless Steel Passivation
Centre Contact Retention Force:	>20N
Contact Pin Material:	Beryllium Copper
Min Coupling Torque:	0.80Nm
Max Coupling Torque:	1.10Nm
Dielectric Withstanding Voltage:	>500V
Durability:	>500 cycles
Flange Mount Length:	15.80mm
Function:	Female Flange Mount RF Connector
Impedance:	50Ohm
Insulation Resistance:	>5000MOhm
Insulator:	UNFILLED ULTEM 1000/PEI
Max Operating Temperature:	+85°C
Min Operating Temperature:	-40°C
Mount Hole Distance:	12.20mm
Min Operating Frequency:	0GHz
Max Operating Frequency:	50GHz
Socket Diameter:	0.23mm
Voltage Max:	150V
Vswr:	<1.30

// Product PDF Links

 [2.40mm Series Product Datasheet](#)

// Product 3D CAD Model Links

 [RF240A2JEGA3D CAD Model](#)



Have a question or project enquiry
you'd like to talk to us about?



[Click Here To Contact Us](#)