


Product Name // SMA Straight Jack 4 Hole Flange RF Connector

 [View Product Page](#)

* Representative product image only





// Product Description:	
 SMA Straight Jack 4 Hole Flange RF Connector	 Dielectric withstanding Voltage: >750V
 Maximum Voltage: 335V	 Impedance: 50Ohm
 Temperature range: -65°C to +165°C	 Body Material: Stainless Steel Passivation
 Frequency range: 0GHz - 26.5GHz	 Contact Material: Beryllium Copper
 VSWR: <1.30	

// General Information:	
Product Display Title:	SMA Series Pin without Extended PTFE 4 Hole Flange
Product Family:	Radio Frequency Connectors
Product Series:	SMA Series
Body Length:	9.40mm
Body Material:	Stainless Steel Passivation
Centre Contact Retention Force:	>26.7N
Contact Pin Material:	Beryllium Copper
Min Coupling Torque:	0.80Nm
Max Coupling Torque:	1.10Nm
Coupling Nut Retention Force:	>27.2Kg
Dielectric Withstanding Voltage:	>750V
Durability:	>500 cycles
Flange Mount Length:	12.70mm
Function:	Female Flange Mount RF Connector
Impedance:	50Ohm
Insulation Resistance:	>5000MOhm
Insulator:	Adapter ASTM D 1710
Max Operating Temperature:	+165°C
Min Operating Temperature:	-65°C
Mount Hole Distance:	8.60mm
Min Operating Frequency:	0GHz
Max Operating Frequency:	26.5GHz
Pin Diameter:	0.64mm
Pin Length:	18.00mm
Thread Size:	1/4 36UNS 2A
Voltage Max:	335V
Vswr:	<1.30

// Product PDF Links

 [SMA Series Product Datasheet](#)

// Product 3D CAD Model Links

 [RFSMAA4JCCDQ3D CAD Model](#)