



Product: [8760ZH](#)

Electronic, 2 C #18 Str TC, PO Ins, OS, LSZH Jkt, CMG

[Request Sample](#)

Product Description

Electronic, 2 Conductor 18AWG (16x30) Tinned Copper, PO Insulation, Overall Beldfoil® Shield, LSZH Outer Jacket, CMG

Technical Specifications

Construction Details

Conductor				
Element	No. of Elements	Size	Stranding	Material
Pair(s)	1	18 AWG	16x30	TC - Tinned Copper

Insulation				
Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Pair(s)	PE - Polyethylene	0.0175 in (0.445 mm)	0.082 in (2.1 mm)	Black & Clear

Outer Shield			
Shield Type	Material	Coverage	Drainwire Type
Tape	Bi-Laminate (Alum+Poly)	100%	20 AWG (7x28) TC

Outer Jacket	
Material	Nom. Thickness
LSZH - Low Smoke Zero Halogen (Flame Retardant)	0.028 in (0.71 mm)
	0.222 in

Overall Cable Diameter (Nominal):	0.222 in.
-----------------------------------	-----------

Electrical Characteristics

Electricals				
Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Nom. Capacitance Cond-to-Other (Conds + Shield)	Nom. Characteristic Impedence	Max. Current
6.5 Ohm/1000ft	29.8 pF/ft (97.8 pF/m)	44 pF/ft (140 pF/m)	57 Ohm	4.8 Amps per Conductor at 25°C

Voltage	
UL Voltage Rating	300 V

Mechanical Characteristics

Temperature	
UL Temperature	Operating
75°C	-20°C To +75°C

Bend Radius	
Stationary Min.	Installation Min.
2.22 in (56.4 mm)	2.22 in

Max. Pull Tension:	62 lbs (28 kg)
Bulk Cable Weight:	26 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor, Non-Halogenated
Flammability / Reaction to Fire:	UL1685 FT4 Loading, FT4
NEC / UL Compliance:	Article 800, CMG
AWM Compliance:	AWM 21305
CEC / C(UL) Compliance:	CMG
ISO/IEC Compliance:	IEC 61034-2 - Smoke Density Min Transmittance = 60%
European Halogen Free Standards:	IEC 62821-1 Halogen Free Compliance = Yes, IEC 60754-1 - Halogen Amount = Zero, IEC 60754-2 - Halogen Acid Gas Amount - Max. Conductivity = 2.5 µS/mm, IEC 60754-2 - Halogen Acid Gas Amount - Min. pH = 4.3
European Directive Compliance:	EU CE Mark, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)

History

Update and Revision:	Revision Number: 0.202 Revision Date: 02-15-2024
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC
8760ZH 060500	Chrome	Reel	500 ft	612825382362
8760ZH 0601000	Chrome	Reel	1,000 ft	612825382355

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.