

9907 Coax - Coaxial Cable - Thinnet 10Base2 Ethernet

For more Information
please call

1-800-Belden1



Description:

20 AWG stranded (19x32) .037" tinned copper conductor, foam polyethylene insulation, Duobond® II (100% coverage) plus an overall tinned copper braid shield (93% coverage), PVC jacket.

Usage (Overall)

Suitable Applications: Thin Ethernet

Physical Characteristics (Overall)

Conductor

AWG:

# Coax	AWG	Stranding	Conductor Material	Dia. (in.)
1	20	19x32	TC - Tinned Copper	.037

Insulation

Insulation Material:

Insulation Material	Dia. (in.)
FHDPE - Foam High Density Polyethylene	.102

Outer Shield

Outer Shield Material:

Layer #	Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
1	Bonded Duofoil®	Tape	Bonded Aluminum Foil-Polyester Tape-Aluminum Foil	100
2		Braid	TC - Tinned Copper	93

Outer Jacket

Outer Jacket Material:

Outer Jacket Material
PVC - Polyvinyl Chloride

Overall Cable

Overall Nominal Diameter: 0.185 in.

Mechanical Characteristics (Overall)

Operating Temperature Range:	-40°C To +80°C
UL Temperature Rating:	60°C (UL AWM Style 1354)
Bulk Cable Weight:	22.300 lbs/1000 ft.
Max. Recommended Pulling Tension:	45 lbs.
Min. Bend Radius (Install)/Minor Axis:	1.800 in.

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification:	CM, CL2
CEC/C(UL) Specification:	CM
AWM Specification:	UL Style 1354 (30 V 60°C)
IEEE Specification:	IEEE802.3 10Base2
Other Standards:	ISO8802.3 10Base2

9907 Coax - Coaxial Cable - Thinnet 10Base2 Ethernet

EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	01/01/2004
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes
Customer Part Number Reference Specification:	DEC Part No. 17-01248-00
RG Type:	58A/U

Flame Test

UL Flame Test:	UL1685 UL Loading
----------------	-------------------

Plenum/Non-Plenum

Plenum (Y/N):	No
Plenum Number:	82907, 89907

Electrical Characteristics (Overall)

Nom. Characteristic Impedance:

Impedance (Ohm)	Tolerance (Ohms)
50	+/- 2

Nom. Capacitance Conductor to Shield:

Capacitance (pF/ft)
25.4

Nominal Velocity of Propagation:

VP (%)
80

Nominal Delay:

Delay (ns/ft)
1.27

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)
8.8

Maximum Loop Resistance:

Resistance (Ohm/1000 ft)
15.24

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/1000 ft)
5.8

Nom. Attenuation:

Freq. (MHz)	Attenuation (dB/100 ft.)
1	.43
10	1.3
50	2.91
100	4.2
200	6.1
400	8.9
700	12.1
900	13.9
1000	14.8

Max. Operating Voltage - UL:

Voltage
300 V RMS
30 V RMS (UL AWM Style 1354)

Notes (Overall)

Notes: Tape to bond at overlap area only. Tape is not designed to bond to dielectric core.

Related Documents:

No related documents are available for this product

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
9907 E4XU1000	1,000 FT	24.000 LB	GRAY, LIGHT DEC		RG-58 TYPE COAX
9907 E4X1000	1,000 FT	25.000 LB	GRAY, LIGHT DEC	C	RG-58 TYPE COAX
9907 E4X1640	1,640 FT	41.000 LB	GRAY, LIGHT DEC	C	RG-58 TYPE COAX
9907 E4X2500	2,500 FT	62.500 LB	GRAY, LIGHT DEC	C	RG-58 TYPE COAX
9907 E4X3280	3,280 FT	82.000 LB	GRAY, LIGHT DEC	C	RG-58 TYPE COAX
9907 E4X500	500 FT	12.500 LB	GRAY, LIGHT DEC		RG-58 TYPE COAX

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 1 Revision Date: 09-23-2008

© 2012 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.