



Datasheet for part number MKJ3C7F7-10CN

|   |
|---|
| Our Catalog Part Number: MKJ3C7F7-10CN  |
| Our Global Manufacturing Part Number: 155402-0102                               |
| Brand: Cannon Product Category: Circular Product Line: Trinity MKJ Series: MKJ3 |

| Product Datasheet           |  |
|-----------------------------|--|
| Series                      | Bayonet Coupling   |
| Class                       | Back- Potted Receptacle  |
| Shell Style                 | Jam Nut Receptacle   |
| Shell Size                  | 7  |
| Plating                     | Aluminum/Electroless Nickel  |
| Contact Arrangement         | 23 Contacts Size 10  |
| Gender                      | Socket, PC Tail, 0.062 Extension   |
| Polarization                | Normal (150° 210°)   |
| Contact Size / Spacing      | #23 / 0.076 inches (1.9 mm)  |
| Wire Acomodiation           | #22 - #28 AWG  |
| Current Rating              | 5 Amps Maximum   |
| Voltage Rating              | 500 VAC RMS Sea Level  |
| Insulator Resitance         | 5000 Megaohms Minimum  |
| Operating Temperature       | -55°/+150°   |
| Contact Resistance          | 8 Milliohms Maximum  |
| Vibration                   | 20 g' in Accordance with MIL-STD-1344 Method 2005, Condition IV                              |
| Shock                       | 300 g' (MKJ1) 50 g' (MKJ0 and MKJ4) in Accordance with MIL-STD-1344 Method 2004, Condition E |
| EMI Shielding Effectiveness | 40dB Attenuation, 100 MHz to 1000 MHz  |