



# Datasheet for part number MKJ4A1W6-7S

|                                                                                 |
|---------------------------------------------------------------------------------|
| Our Catalog Part Number: MKJ4A1W6-7S                                            |
| Our Global Manufacturing Part Number: 155281-1043                               |
| Brand: Cannon Product Category: Circular Product Line: Trinity MKJ Series: MKJ4 |

| Product Datasheet           |                                                                                              |
|-----------------------------|----------------------------------------------------------------------------------------------|
| Series                      | Breakaway / Quick Disconnect                                                                 |
| Class                       | Environmental Plug and Receptacle with Banding/Overmolding Platform                          |
| Shell Style                 | In-Line Receptacle                                                                           |
| Shell Size                  | 1                                                                                            |
| Plating                     | Aluminum/OD Cad                                                                              |
| Contact Arrangement         | 23 Contacts Size 7                                                                           |
| Gender                      | Socket, Crimp, Removable                                                                     |
| Polarization                | Normal (150° 210°)                                                                           |
| Contact Size / Spacing      | #23 / 0.076 inches (1.9 mm)                                                                  |
| Wire Acomodiation           | #22 - #28 AWG                                                                                |
| Current Rating              | 5 Amps Maximum                                                                               |
| Voltage Rating              | 500 VAC RMS Sea Level                                                                        |
| Insulator Resitance         | 5000 Megaohms Minimum                                                                        |
| Operating Temperature       | -55°/+150°                                                                                   |
| Contact Resistance          | 8 Milliohms Maximum                                                                          |
| Vibration                   | 20 g' in Accordance with MIL-STD-1344 Method 2005, Condition IV                              |
| Shock                       | 300 g' (MKJ1) 50 g' (MKJ0 and MKJ4) in Accordance with MIL-STD-1344 Method 2004, Condition E |
| EMI Shielding Effectiveness | 40dB Attenuation, 100 MHz to 1000 MHz                                                        |