



Part Number: 1419A

RS-232/422 Low Cap, #24-2pr, FPO, O/A Foil, PVC Jkt, CM, 100Ω

Product Description

Computer EIA RS-232/422 Cable, 24 AWG stranded (7x32) tinned copper conductors, Datalene® insulation, twisted pairs, overall Beldfoil® shield (100% coverage), 24 AWG stranded tinned copper drain wire, PVC jacket.

Technical Specifications

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	No. of Conductors	No. of Pairs
24	7x32	TC - Tinned Copper	4	2

Conductor Count: 4

Insulation

Material	Material Trade Name	Nominal Wall Thickness
FPE - Foamed Polyethylene	Datalene®	0.013 in

Color Chart

Number	Color
1	White/Blue & Blue/White
2	White/Orange & Orange/White

Outer Shield Material

Type	Material	Material Trade Name	Coverage [%]	Drainwire Material	Drainwire AWG	Drainwire Construction n x D
Tape	Aluminum/Polyester	Beldfoil®	100 %	TC - Tinned Copper	24	7x32 mm

Outer Jacket Material

Material	Nominal Diameter	Nominal Wall Thickness
PVC - Polyvinyl Chloride	0.248 in	0.035 in

Electrical Characteristics

Conductor DCR

Nominal Conductor DCR	Nominal Outer Shield DCR
24 Ohm/1000ft	15.1 Ohm/1000ft

Capacitance

Nom. Capacitance Conductor to Conductor	Nom. Capacitance Conductor to Other Conductor to Shield
13 pF/ft	22 pF/ft

Inductance

Nominal Inductance
0.21 μH/ft

Impedance

Nominal Characteristic Impedance
100 Ohm

Delay

Max. Delay Skew	Nominal Velocity of Propagation (VP) [%]
78 ns/100m	78 %

Current

Max. Recommended Current [A]
1.8 Amps per conductor @ 25°C A

Voltage

UL Voltage Rating
30 V RMS (UL AWM Style 2919); 300 V RMS

Temperature Range

Operating Temp Range:	-20°C To +80°C
-----------------------	----------------

Mechanical Characteristics

Bulk Cable Weight:	27 lbs/1000ft
Max Recommended Pulling Tension:	22 lbs
Min Bend Radius/Minor Axis:	2.5 in

Standards

NEC Articles:	800
NEC/(UL) Specification:	CM
CEC/C(UL) Specification:	CM
UL AWM Style:	2919 (30 V 80°C)
CPR Euroclass:	Eca

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2004-01-01
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Flammability, LSOH, Toxicity Testing

UL Flammability:	UL1685 UL Loading
CSA Flammability:	FT1
ISO/IEC Flammability:	IEC 60332-1-2
UL voltage rating:	30 V RMS (UL AWM Style 2919); 300 V RMS

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Part Number

Variants

Item #	Color	UPC	Footnote
1419A 0601000	Chrome	612825114949	C
1419A 06010000	Chrome	612825114956	C Y
1419A 060500	Chrome	612825114963	C

Footnote:	C - CRATE REEL PUT-UP.
Footnote:	Y - FINAL PUT-UP LENGTH MAY VAR -10% TO +20% FROM LENGTH SHOWN. MAY CONTAIN 2 PIECES. MINIMUM LENGTH OF ANY ONE PIECE IS 1500'.

Product Notes

Notes:	Datalene« insulation features include low dielectric constant and a dissipation factor for high-speed, low distortion data handling. Physical properties include good crush resistance and light weight.
--------	----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------

History

Update and Revision:	Revision Number: 0.297 Revision Date: 08-22-2019
----------------------	--------------------------------------------------

© 2019 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.