



**Part Number: 9451P**

Audio Cable, #22-2c, TC, O/A Foil, CMP

## Product Description

Audio Cable, Plenum-CMP, 1-22 AWG stranded tinned copper pair, FEP insulation, Beldfoil® shield, drain, Flamarrest® jacket

## Technical Specifications

### Product Overview

Environmental Space:	Indoor - Plenum
----------------------	-----------------

### Physical Characteristics (Overall)

#### Conductor

AWG	Stranding	Material	No. of Pairs
22	7x30	TC - Tinned Copper	1

Conductor Count:	2
Total Number of Pairs:	2
Conductor Size:	22 AWG

#### Insulation

Material	Nominal Diameter	Nominal Wall Thickness
FEP - Fluorinated Ethylene Propylene	0.044 in	0.007 in

#### Color Chart

Number	Color
1	Black & Red

#### Outer Shield Material

Type	Material	Material Trade Name	Coverage [%]	Drainwire Material	Drainwire AWG	Drainwire Construction n x D
Tape	Aluminum Foil-Polyester Tape	Beldfoil®	100 %	TC - Tinned Copper	22	7x30 mm

#### Outer Jacket Material

Material	Material Trade Name	Nominal Diameter
LS PVC - Low Smoke Polyvinyl Chloride	Flamarrest®	0.127 in

### Electrical Characteristics

#### Conductor DCR

Nominal Conductor DCR	Nominal Outer Shield DCR
14.1 Ohm/1000ft	14.3 Ohm/1000ft

#### Capacitance

Nom. Capacitance Conductor to Conductor	Nom. Capacitance Conductor to Other Conductor to Shield
35 pF/ft	67 pF/ft

Shielding:	Foil(s) or Copper Tape(s)
------------	---------------------------

#### Inductance

Nominal Inductance
0.15 µH/ft

#### Delay

Nominal Delay	Nominal Velocity of Propagation (VP) [%]
1.47 ns/ft	69 %

#### Current

Max. Recommended Current [A]
2.9 Amps per conductor @ 25°C

#### Voltage

UL Voltage Rating
300 V RMS

#### Temperature Range

UL Temp Rating:	60°C
Operating Temp Range:	-20°C To +75°C

#### Mechanical Characteristics

Bulk Cable Weight:	14 lbs/1000ft
Max Recommended Pulling Tension:	27 lbs
Min Bend Radius/Minor Axis:	1.25 in

#### Standards

NEC/(UL) Specification:	CMP
CEC/C(UL) Specification:	CMP
CPR Euroclass:	Eca

#### Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2005-04-01
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

#### Suitability

Suitability - Aerial:	No
Suitability - Burial:	No
Suitability - Hazardous Locations:	No
Suitability - Indoor:	Yes
Suitability - Outdoor:	No
Suitability - Sunlight Resistance:	No

#### Flammability, LS0H, Toxicity Testing

UL Flammability:	NFPA 262
CSA Flammability:	FT6
UL voltage rating:	300 V RMS

#### Plenum/Non-Plenum

Plenum (Y/N):	Yes
---------------	-----

#### Part Number

Non-Plenum Number:	9451
--------------------	------

#### Variants

Item #	Color	Footnote
9451P 0101000	Black	
9451P 0105000	Black	C
9451P 010U1000	Black	

9451P 010500	Black	
9451P 010500	Black	
9451P 006U1000	Blue, Light	
9451P 0015000	Brown	C
9451P 001U1000	Brown	
9451P 0085000	Gray	C
9451P 008U1000	Gray	
9451P N3U5000	Green, Mil	C
9451P N3UU1000	Green, Mil	
9451P 0035000	Orange	C
9451P 003U1000	Orange	
9451P 0025000	Red	C
9451P 002U1000	Red	
9451P 0075000	Violet	C
9451P 007U1000	Violet	
9451P 0095000	White	C
9451P 009U1000	White	
9451P 0045000	Yellow	C
9451P 004U1000	Yellow	
9451P 0065000	Yellow	C

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

© 2018 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.